










PART MUNBER
SEE SHEET 2



spec ref -				dr		Li-Qing Lei	2014/11/20	projection 		mm 		size		A3	scale		10:1												
tolerance std				eng		Li-Qing Lei	2017/01/05					ecn no		-															
TOLERANCES UNLESS OTHERWISE SPECIFIED				chr		-						-		-															
ISO 406				appr		Tim Yao		2017/01/05	product family						-		rel level		Released										
ISO 1101																													
surface 		linear		0.X		±0.25		Amphenol FCi						title		USB3.1 Type-C						dwg no		10132328		rev		A	
				0.XX		±0.15																							
				0.XXX		±0.10																							
ISO 1302		angular		0°		±2°								cat. no.		-		Product - Customer Drw						sheet 1 of 3					

- NOTE:
- MATERIAL:
 - HSG: THERMOPLASTIC, BLACK, UL94-V0
 - TERMINAL: COPPER ALLOY
 - EMI PLATE: STAINLESS STEEL
 - MID PLATE: STAINLESS STEEL
 - SHIELD: STAINLESS STEEL
 - PLATING:
 - TERMINAL: (Min) 0.05 μm Au + (Min) 0.75 μm Ni-Pd ON CONTACT AREA
 - SHELL: PLATING 0.74 μm MIN Ni OVER AREA.
 - EMI: PLATING 0.74 μm MIN Ni OVER AREA.
 - CENTER PLATE: PLATING 0.74 MIN Ni OVER AREA.
 - MECHANICAL CHARACTER:
 - INSERTION FORCE: 5~20N;
 - EXTRACTION FORCE: 8~20N INITIAL, 6~20N AFTER DURABILITY;
 - DURABILITY: 10,000 CYCLES;
 - OPERATION TEMPERATURE: -55°C TO +85°C
 - ELECTRICAL CHARACTER:
 - LLCR : 40m Ω INITIAL, 50m Ω MAX AFTER ENVIRONMENT TEST;
 - INSULATION RESISTANCE: 100M Ω MIN AT 250V DC.
 - DIELECTRIC WITHSTAND VOLTAGE: 100VAC MIN.
 - THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW ;
 - LEAD FREE PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DISCRIBLED IN GS-22-008
 - PRODUCT SPEC: GS-12-1299
 - SOLDER TAILL TO BE COPLANAR WITHIN 0.10 TO EACH OTHER


PRODUCT NUMBER CODE:
10132328-100XXLF

- THE LENGTH OF SHELL'S LEG OPTION
- DIM"A"=1.2 WITH 6 SMT TAILS IN THE MIDDLE
 - DIM"A"=1.6 WITH 6 SMT TAILS IN THE MIDDLE
 - DIM"A"=1.2 WITHOUT 6 SMT TAILS IN THE MIDDLE
 - DIM"A"=1.6 WITHOUT 6 SMT TAILS IN THE MIDDLE


GROUND PIN STATUS (A1/A12/B1/B12)

- SEPARATED
- CONNECTED

AVAILABLE P/N:
10132328-10001LF
10132328-10011LF
10132328-10013LF



6 SMT TAILS






PIN ASSIGNMENTS

PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A2	SSTXp1	B11	SSRXp1
A3	SSTXn1	B10	SSRXn1
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A10	SSRXn2	B3	SSTXn2
A11	SSRXp2	B2	SSTXp2
A12	GND	B1	GND

NOTE: TX AND RX ARE DEFINED FORM THE HOST PERSPECTIVE

spec ref	-	dr	Li-Qing Lei	2014/11/20	projection	mm	size	A3	scale	10:1
tolerance std	ISO 406 ISO 1101	eng	Li-Qing Lei	2017/01/05	chr	-	ecn no	-	rel level	Released
surface	linear	appr	Tim Yao	2017/01/05	product family	USB3.1 Type-C	cat. no.	Product - Customer Drw	sheet 2 of 3	rev
	angular					Vertical, Receptacle				A

TAPE REEL PACKAGE
Q'TY: (350)EA/REEL



SHOWS THE METHOD OF COVER TAPE'S PEELING FORCE MEASUREMENT.
PEELING FORCE MUST BE 0.1 TO 1.3N AT THE SPEED OF 300MM/MIN.

spec ref	-	dr	Li-Qing Lei	2014/11/20	projection	mm	size	A3	scale	1:1
tolerance std	ISO 406 ISO 1101	eng	Li-Qing Lei	2017/01/05	chr	-	ecn no	-	rel level	Released
surface	linear	appr	Tim Yao	2017/01/05	product family	USB3.1 Type-C	dwg no	10132328	rev	A
ISO 1302	angular				cat. no.	Vertical, Receptacle	Product - Customer Drw	sheet 3 of 3		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[FCI / Amphenol:](#)

[10132328-10011LF](#) [10132328-10013LF](#) [10132328-10014LF](#) [10132328-10001LF](#)