


Sep.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




Note. 1. Lead co-planarity shall be 0.1mm MAX.
2. Please consult Hirose when the product is mounted to FPC.


Sep.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

Drawing for packing(FREE)

Number of conductor:2, 3, 4, 5, 10, 12, 16, 18, 20




Style and dimension of reel (FREE)




Part No.	Code No.	F	G	H	J
DF53-2S-0.6H	CL0668-1001-0-00	7.5	16	17.4	21.4
DF53-3S-0.6H	CL0668-1002-0-00	7.5	16	17.4	21.4
DF53-4S-0.6H	CL0668-1003-0-00	7.5	16	17.4	21.4
DF53-5S-0.6H	CL0668-1004-0-00	7.5	16	17.4	21.4
DF53-10S-0.6H	CL0668-1007-0-00	11.5	24	25.4	29.4
DF53-12S-0.6H	CL0668-1008-0-00	11.5	24	25.4	29.4
DF53-16S-0.6H	CL0668-1010-0-00	11.5	24	25.4	29.4
DF53-18S-0.6H	CL0668-1011-0-00	11.5	24	25.4	29.4
DF53-20S-0.6H	CL0668-1012-0-00	11.5	24	25.4	29.4

5 Taping(FREE)



Reflow temperature profile in resistance to soldering heat




Number of reflow cycles 2 cycles MAX.

- Note
- 1 reel:5,000 connectors.
 - () is reference dimension.
 - Refer to IEC 60286-3 and JIS C 0806-3. (Packaging of components for automated handling)
 - This product satisfies halogen free requirements defined as 900 ppm maximum chlorine, 900 ppm maximum bromine, and 1500 ppm maximum total of chlorine and bromine.
 - Refer to the technical specification(ETAP-H1068) for packing type.
 - Please make sure refer to the manuals below for operation of this product.
For operation manual ETAD-H0996-00

HRS	DRAWING NO.	EDCX-402844-00-00
	PART NO.	DF53-S-0.6H
	CODE NO.	CL0010-0630-0-00
	NO.	2/3

Style and dimension of reel (FREE)



Technical drawing of a cable reel assembly. The drawing includes a side view of the reel with a cable being unreeled, a cross-sectional view of the reel housing, and a cross-sectional view of the cable reel assembly. The side view shows the cable being unreeled in the direction of unreeing, indicated by an arrow. The cross-sectional view of the reel housing shows a dimension of $+0.0$ to -0.0 for the G dimension. The cross-sectional view of the cable reel assembly shows a dimension of 2 for the leader. The drawing is labeled "Drawing (FREE)" and "HRS DRAWING FOR REFERENCE".


Part
DF53-6
DF53-8
DF53-14

Direction of unreeing

ing (FREE)

Leader
400mm MIN

Reflow temperature profile in resistance to solderring heat



Number of reflow cycles 2 cycles MAX.

- | | | | | |
|---|-------------|-------------------|---|---|
|  | DRAWING NO. | EDCX-402844-00-00 | | |
| | PART NO. | DF53-S-0. 6H | | |
| | CODE NO. | CL0010-0630-0-00 |  |  |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF53-18S-0.6H](#)