



Assembly instruction see N 22 091 0023

Number of contacts	Standard	3	4	5	5	6	7	7	8	12	14	14	19
Contact arrangement	IEC 61076-2-106	03-a	04-a	05-a	05-b	06-a	07-a	07-b	08-a	12-a	14-a	14-b	19-a
Rated voltage	IEC 60664-1	150 V	100 V	32 V	100 V	32 V							
Rated impulse withstand voltage	IEC 60664-1	1500 V	800 V	1500 V	800 V								
Pollution degree	IEC 60664-1	3 <sup>1)</sup>											
Installation category	IEC 60664-1	I											
Insulation group	IEC 60664-1	II, 400 ≤ CTI < 600											
Current rating	IEC 60512-5-2 UL 1977	10A/+40°C	7A/+40°C					3A/+40°C					
Insulation resistance	IEC 60512-3-1	>10 <sup>10</sup> Ohm <sup>2)</sup>											
Contact resistance	IEC 60512-2-1	<5mOhm											
Climatic category	IEC 60668-1	40 / 100 / 21											
Temperatur range	IEC 60668-1	-40°C...+100°C / -40°F...+212°F											
Salt spray resistance	DIN IEC 60068-2-11, test Ka	720h											
IP degree	IEC 60529	IP69K / IP 68 (in mated condition)											
Insertion and withdrawal force	IEC 60512-13-2	25N	30N	35N	35N	50N	55N	55N	60N	50N	50N	50N	60N
mechanical operation	IEC 60512-9-1	Silver ≥500 mating cycles / Gold ≥1000 mating cycles											
housing material		brass and / or zinc die cast, nickel plated											
dielectric material		thermoplastic											
sealing material		Chloroprene											
contacts		silver or gold plated											
termination technique		solder											
wire gauge		≤0,5mm <sup>2</sup> / 20 AWG					≤0,35mm <sup>2</sup> / 22 AWG						
flamability		UL 94 V0											
locking system	DIN EN 61076-2-106	metal screw coupling, tightening torque 0,7 - 1,5 Nm											

<sup>1)</sup> designed according pollution degree 2, can be used under pollution degree 3 if the rules according IEC 60664-1 are fulfilled  
<sup>2)</sup> under operating conditions >10<sup>8</sup> Ohm

Do not connect or disconnect under load. Metal housing parts shall be securely incorporated to protected ground.

Remark for gold plated contacts:

In order to avoid brittle inter-metallic connections, gold plated terminals have to be tin-plated in the solder area. All technical data have been measured in a laboratory environment and can be different during practical usage of the product. Any product information is for descriptive usage only and not legally binding; particularly the information does not constitute or provide any legal guaranties ("Beschaffensgarantie" or "Haltbarkeitsgarantie").

03	202000083	26.10.2020	MCARL
Index	Änderung/Description	Datum/Date	Name

	19 (19-a)	C091 31H019 100 4 U	C091 31H019 200 4 U
	14 (14-b)	C091 31H114 100 4 U	C091 31H114 200 4 U
	14 (14-a)	C091 31H014 100 4 U	C091 31H014 200 4 U
	12 (12-a)	C091 31H012 100 4 U	C091 31H012 200 4 U
	8 (08-a)	C091 31H008 100 4 U	C091 31H008 200 4 U
	7 (07-b)	C091 31H107 100 4 U	C091 31H107 200 4 U
	7 (07-a)	C091 31H007 100 4 U	C091 31H007 200 4 U
	6 (06-a)	C091 31H006 100 4 U	C091 31H006 200 4 U
	5 (05-b)	C091 31H105 100 4 U	C091 31H105 200 4 U
	5 (05-a)	C091 31H005 100 4 U	C091 31H005 200 4 U
	4 (04-a)	C091 31H004 100 4 U	C091 31H004 200 4 U
	3 (03-a)	C091 31H003 100 4 U	C091 31H003 200 4 U

Contact arrangement View on mating side	Number of contacts (Contact arrangement acc. IEC 61076-2-106)	Part number with silver plated contacts	Part number with gold plated contacts
--	---	---	---

Gewicht (errechnet) / Calc WT: 0,05 kg	Zul. Abw./Tolerances:	Maßstab / Scale: 2:1	A3	
Prüfmaß / Testdimension	ISO 2768-c	CUSTOMER DRAWING		
Teileindex / Partindexnumber:	DIN / ISO 13715			
Bagatelle change:				

Gez.	26.05.2020	Male cable connector for cable diameter 4-6 mm
Drawn	MCARLE	
Status	Released	
Gepr.	11.01.2021	
Checked	MBERTSCH	

<b>Amphenol Tuchel Industrial GmbH</b>		M C091 31HXXX X00 4 U	Blatt/Sheet 1
--	--	-----------------------	------------------

Ers. f. / Replacement for: M-C091 31HXXX X00 4 U Rev02
--

Weitergabe sowie Vervielfältigung dieser Unterlage, Verwertung und Mitteilung ihres Inhalts nicht gestattet, soweit nicht ausdrücklich zugestanden. Zuwiderhandlungen verpflichten zu Schadensersatz. Alle Rechte für den Fall der Patenterteilung oder Gebrauchsmuster-Eintragung vorbehalten.

FAI2020-001731  
NXM-V02

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[C091 31H014 100 4](#)