



- NOTES
- ① One example of the rotation of Ref. No. ⑤ to Ref. No. ① is shown.
 - ② The recommended torque of Ref. No. ⑤ : 2 TO 3 N·m.
 - ③ Across flats hexagon head of Ref. No. :1.27 the recommended clamp torque of Ref. No. ⑧ : 0.3 to 0.4 N·m.
 - ④ The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.
 - ⑤ LOCTITE 243 HENKEL JAPAN or equivalent is recommended to prevent Ref. No. ①, ⑦ and ⑧ for loosening.

4	DIALLYL PHTHALATE	(BLACK) UL94V-0	8	STEEL	NICKEL PLATING	HEXAGON SOCKET SET SCREW M2. 6X0. 45X2
3	DIALLYL PHTHALATE	(BLACK) UL94V-0	7	BRASS	NICKEL PLATING	JIS B 1101 M2X0. 4X8
2	COPPER ALLOY	SILVER PLATING 2 μ m min.	6	ZINC ALLOY	MATTE FINISH NICKEL PLATED	
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	ZINC ALLOY	MATTE FINISH NICKEL PLATED	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
HIROSE ELECTRIC CO., LTD.		APPROVED :HY. KOBAYASHI 15.10.27	CHECKED :HY. KOBAYASHI 15.10.27	DESIGNED :HT. ZENBA 15.10.26	DRAWN :HT. ZENBA 15.10.26	DRAWING NO. EDC-027937-00-00	PART NO. RM12BJB-5PH
				CODE NO. CL109-0832-9-00	1/1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[RM12BJB-5PH](#)