






Jun.1.2019 Copyright 2019 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV. RoHS COMPLIANT



RECOMMENDED PC BOARD PATTERN



|                                      |          |                  |           |                                     |                               |
|--------------------------------------|----------|------------------|-----------|-------------------------------------|-------------------------------|
| 1                                    | PBT      | UL94V-0          | 2         | BRASS                               | TIN PLATING                   |
| NO.                                  | MATERIAL | FINISH . REMARKS | NO.       | MATERIAL                            | FINISH . REMARKS              |
| UNITS<br>mm                          |          | SCALE<br>2 : 1   | COUNT<br> | DESCRIPTION OF REVISIONS            | DESIGNED                      |
|                                      |          |                  |           | CHECKED                             | DATE                          |
| <b>HRS</b> HIROSE ELECTRIC CO., LTD. |          |                  |           | APPROVED : AR. SHIRAI 10.09.06      | DRAWING NO. EDC3-084094-01    |
|                                      |          |                  |           | CHECKED : AR. SHIRAI 10.09.06       | PART NO. GT3B-16DP-2.5DSA<70> |
|                                      |          |                  |           | DESIGNED : NA. HARUBAYASHI 10.09.06 | CODE NO. CL753-0003-1-70      |
|                                      |          |                  |           | DRAWN : Chinoik.Ng 10.09.06         | 1/1                           |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[GT3B-16DP-2.5DSA\(70\)](#)