



NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-S-8805 SYMBOL 4
- 3 - CIRCUIT DIAGRAM AND CATALOG LISTING ARE SHOWN ON NAMEPLATE
- 4 - COINCIDENCE OF OPERATING AND RELEASING POINTS: .010 OF PLUNGER TRAVEL

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE	6-12 LB	CONTACT ARRANGEMENT		DO NOT SCALE PRINT
FULL OVERTRAVEL FORCE	30 LB MAX	S P D T (2)		
RELEASE FORCE	4 LB MIN	LOAD		UNLESS OTHERWISE NOTED
PRETRAVEL	.040 MAX	28 VDC		DIMENSIONS ARE IN INCHES
DIFFERENTIAL TRAVEL	.020 MAX	SEA LEVEL	50,000 FT.	TOLERANCES ARE:
OVERTRAVEL	.250 MIN	RES	4	ONE PLACE (.0) ±.030
		IND	2	TWO PLACE (.00) ±.015
		MOTOR	4	THREE PLACE (.000) ±.005
				ANGLES ±
				WEIGHT 11.0 OZ MAX

DRAWING NUMBER: 1EN204-15B
 ISSUE: 10
 REVISIONS:
 A CO4435i PART 7 WJM 2 APR 79
 CHECK: CE 3 1 APR 79
 DRAWN: WJM 2 APR 79
 FC-50378-003

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1EN204-15B](#)