


Oct.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



Part No.	Code No.	A	B	C
DF53-2P-0.6C	CL0668-1013-0-00	2.9	1.8	0.6
DF53-3P-0.6C	CL0668-1014-0-00	3.5	2.4	1.2
DF53-4P-0.6C	CL0668-1015-0-00	4.1	3.0	1.8
DF53-5P-0.6C	CL0668-1016-0-00	4.7	3.6	2.4
DF53-6P-0.6C	CL0668-1017-0-00	5.3	4.2	3.0
DF53-8P-0.6C	CL0668-1018-0-00	6.5	5.4	4.2
DF53-10P-0.6C	CL0668-1019-0-00	7.7	6.6	5.4
DF53-12P-0.6C	CL0668-1020-0-00	8.9	7.8	6.6
DF53-14P-0.6C	CL0668-1021-0-00	10.1	9.0	7.8
DF53-16P-0.6C	CL0668-1022-0-00	11.3	10.2	9.0
DF53-18P-0.6C	CL0668-1023-0-00	12.5	11.4	10.2
DF53-20P-0.6C	CL0668-1024-0-00	13.7	12.6	11.4

- 注 1 . Per pack:100 pieces.
- ② A number of slits varies depending on pin count.  
 - 2 slits for 2 to 12 pos. (No.1, No.N)  
 - 4 slits for 14 to 20 pos. (No.1, No.4, No.N-3, No.N)
- 3 . This product satisfies halogen free requirements defined as 900 ppm maximum chlorine, 900 ppm maximum bromine, and 1500 ppm maximum total of chlorine and bromine.
- 4 . Refer to the technical specification(ETAP-H1051-00) for the packing type.
- 5 . Please make sure refer to the manuals below for operation of this product.  
 For cable assembly procedure ETAD-H0995-00  
 For operation manual ETAD-H0996-00

1	PA 9T	BLACK, UL94V-0			
NO.	MATERIAL	FINISH	REMARKS		
UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED
mm	10:1	0			
APPROVED : SJ. OKAMURA 2024.06.21			DRAWING NO. EDCX-407144-00-00		
CHECKED : SJ. OKAMURA 2024.06.21			PART NO. DF53-P-0.6C		
DESIGNED : JN. TONAI 2024.06.21			CODE NO. CL0010-0636-0-00		
DRAWN : JN. TONAI 2024.06.21			DATE 2023.03.29		

FORM HC0011-5

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[DF53-2P-0.6C](#)