



OptiMOS™ Small-Signal-Transistor
Features

- N-channel
- Enhancement mode
- Logic Level (4.5V rated)
- Avalanche rated
- Qualified according to AEC Q101
- 100% lead-free; RoHS compliant
- Halogen-free according to IEC61249-2-21

Product Summary

| | | | |
|------------------|-----------------------|------|----------|
| V_{DS} | | 100 | V |
| $R_{DS(on),max}$ | $V_{GS}=10\text{ V}$ | 0.23 | Ω |
| | $V_{GS}=4.5\text{ V}$ | 0.27 | |
| I_D | | 1.8 | A |


PG-SOT223


| Type | Package | Tape and Reel | Marking | Halogen-Free | Packing |
|---------|---------|-----------------------|---------|--------------|---------|
| BSP372N | SOT223 | H6327: 1000 pcs/ reel | BSP372N | Yes | Non dry |

Maximum ratings, at $T_j=25\text{ °C}$, unless otherwise specified

| Parameter | Symbol | Conditions | Value | Unit |
|-------------------------------------|-------------------|--|-------------|-------------------|
| Continuous drain current | I_D | $T_A=25\text{ °C}$ | 1.8 | A |
| | | $T_A=70\text{ °C}$ | 1.5 | |
| Pulsed drain current | $I_{D,pulse}$ | $T_A=25\text{ °C}$ | 7.2 | |
| Avalanche energy, single pulse | E_{AS} | $I_D=1.8\text{ A}$, $R_{GS}=25\ \Omega$ | 33 | mJ |
| Reverse diode dv/dt | dv/dt | $I_D=1.8\text{ A}$, $V_{DS}=80\text{ V}$, $di/dt=200\text{ A}/\mu\text{s}$, $T_{j,max}=150\text{ °C}$ | 6 | kV/ μs |
| Gate source voltage | V_{GS} | | ± 20 | V |
| Power dissipation ¹⁾ | P_{tot} | $T_A=25\text{ °C}$ | 1.8 | W |
| Operating and storage temperature | T_j , T_{stg} | | -55 ... 150 | °C |
| ESD Class | | JESD22-A114 -HBM | 0 (<250V) | |
| Soldering Temperature | | | 260 °C | |
| IEC climatic category; DIN IEC 68-1 | | | 55/150/56 | |

| Parameter | Symbol | Conditions | Values | | | Unit |
|-----------|--------|------------|--------|------|------|------|
| | | | min. | typ. | max. | |

Thermal characteristics

| | | | | | | |
|---|------------|--|---|---|-----|-----|
| Thermal resistance junction - soldering point | R_{thJS} | | - | - | 25 | K/W |
| Thermal resistance junction - ambient | R_{thJA} | minimal footprint | - | - | 110 | |
| | | 6 cm ² cooling area ¹⁾ | - | - | 70 | |

Electrical characteristics, at $T_j=25\text{ °C}$, unless otherwise specified
Static characteristics

| | | | | | | |
|---------------------------------|---------------|---|-----|-----|------|------------------|
| Drain-source breakdown voltage | $V_{(BR)DSS}$ | $V_{GS}=0\text{ V}, I_D=250\text{ }\mu\text{A}$ | 100 | - | - | V |
| Gate threshold voltage | $V_{GS(th)}$ | $V_{DS}=V_{GS}\text{ V}, I_D=218\text{ }\mu\text{A}$ | 0.8 | 1.4 | 1.80 | |
| Drain-source leakage current | I_{DSS} | $V_{DS}=100\text{ V}, V_{GS}=0\text{ V}, T_j=25\text{ °C}$ | - | - | 0.1 | μA |
| | | $V_{DS}=100\text{ V}, V_{GS}=0\text{ V}, T_j=150\text{ °C}$ | - | - | 10 | |
| Gate-source leakage current | I_{GSS} | $V_{GS}=20\text{ V}, V_{DS}=0\text{ V}$ | - | - | 10 | nA |
| Gate-source on-state resistance | $R_{DS(on)}$ | $V_{GS}=10\text{ V}, I_D=1.8\text{ A}$ | - | 153 | 230 | $\text{m}\Omega$ |
| | | $V_{GS}=4.5\text{ V}, I_D=1.7\text{ A}$ | - | 172 | 270 | |
| Transconductance | g_{fs} | $ V_{DS} >2 I_D R_{DS(on)max}, I_D=1.5\text{ A}$ | | 5.1 | - | S |

¹⁾ Device on 40mm x 40mm x 1.5mm epoxy PCB FR4 with 6cm² (one layer, 70 μm thick) copper area for drain connection. PCB is vertical in still air.

| Parameter | Symbol | Conditions | Values | | | Unit |
|-----------|--------|------------|--------|------|------|------|
| | | | min. | typ. | max. | |

Dynamic characteristics

| | | | | | | |
|------------------------------|--------------|--|---|------|------|----|
| Input capacitance | C_{iss} | $V_{GS}=0\text{ V}, V_{DS}=25\text{ V},$ $f=1\text{ MHz}$ | - | 247 | 329 | pF |
| Output capacitance | C_{oss} | | - | 40 | 54 | |
| Reverse transfer capacitance | C_{rss} | | - | 19 | 28 | |
| Turn-on delay time | $t_{d(on)}$ | $V_{DD}=50\text{ V}, V_{GS}=10\text{ V},$ $I_D=1.8\text{ A}, R_{G,ext}=6\ \Omega$ | - | 5.1 | 7.7 | ns |
| Rise time | t_r | | - | 6.7 | 10.1 | |
| Turn-off delay time | $t_{d(off)}$ | | - | 47.3 | 71.0 | |
| Fall time | t_f | | - | 18 | 27 | |

Gate Charge Characteristics


| | | | | | | |
|-----------------------|---------------|---|---|-----|------|----|
| Gate to source charge | Q_{gs} | $V_{DD}=50\text{ V}, I_D=1.8\text{ A},$ $V_{GS}=0\text{ to }10\text{ V}$ | - | 0.6 | 0.9 | nC |
| Gate to drain charge | Q_{gd} | | - | 3.0 | 4.5 | |
| Gate charge total | Q_g | | - | 9.5 | 14.3 | |
| Gate plateau voltage | $V_{plateau}$ | | - | 2.3 | - | V |

Reverse Diode

| | | | | | | |
|----------------------------------|---------------|--|---|------|------|----|
| Diode continuous forward current | I_S | $T_A=25\text{ }^\circ\text{C}$ | - | - | 1.8 | A |
| Diode pulse current | $I_{S,pulse}$ | | - | - | 7.2 | |
| Diode forward voltage | V_{SD} | $V_{GS}=0\text{ V}, I_F=1.8\text{ A},$ $T_j=25\text{ }^\circ\text{C}$ | - | 0.82 | 1.1 | V |
| Reverse recovery time | t_{rr} | $V_R=50\text{ V}, I_F=1.8\text{ A},$ $di_F/dt=100\text{ A}/\mu\text{s}$ | - | 38 | 57 | ns |
| Reverse recovery charge | Q_{rr} | | - | 51.5 | 77.3 | nC |


1 Power dissipation

$P_{tot}=f(T_A)$



2 Drain current


$I_D=f(T_A); V_{GS} \geq 10\text{ V}$



3 Safe operating area

$I_D=f(V_{DS}); T_A=25\text{ °C}; D=0$


parameter: t_p



4 Max. transient thermal impedance

$Z_{thJA}=f(t_p)$


parameter: $D=t_p/T$



5 Typ. output characteristics

$I_D=f(V_{DS}); T_j=25\text{ }^\circ\text{C}$


parameter: V_{GS}



6 Typ. drain-source on resistance


$R_{DS(on)}=f(I_D); T_j=25\text{ }^\circ\text{C}$

parameter: V_{GS}




7 Typ. transfer characteristics

$I_D=f(V_{GS}); |V_{DS}|>2|I_D|R_{DS(on)max}$




8 Typ. forward transconductance

$g_{fs}=f(I_D); T_j=25\text{ }^\circ\text{C}$



9 Drain-source on-state resistance


$R_{DS(on)}=f(T_j)$; $I_D=1.8\text{ A}$; $V_{GS}=10\text{ V}$



10 Typ. gate threshold voltage


$V_{GS(th)}=f(T_j)$; $V_{DS}=V_{GS}$; $I_D=218\ \mu\text{A}$

parameter: I_D



11 Typ. capacitances


$C=f(V_{DS})$; $V_{GS}=0\text{ V}$; $f=1\text{ MHz}$; $T_j=25^\circ\text{C}$



12 Forward characteristics of reverse diode

$I_F=f(V_{SD})$


parameter: T_j



13 Avalanche characteristics

$I_{AS}=f(t_{AV}); R_{GS}=25 \Omega$


parameter: $T_{j(\text{start})}$



14 Typ. gate charge


$V_{GS}=f(Q_{\text{gate}}); I_D=1.8 \text{ A pulsed}$

parameter: V_{DD}




15 Drain-source breakdown voltage

$V_{BR(DSS)}=f(T_j); I_D=250 \mu\text{A}$






16 Gate charge waveforms



SOT223

Package Outline:



Published by
Infineon Technologies AG
81726 Munich, Germany
© 2011 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office. Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Infineon:](#)

[BSP372NH6327XTSA1](#)