








ELV. RoHS COMPLIANT





MATED CONNECTORS

- NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)  
 USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN  
 NO. OF CYCLES : 2 MAX  
 PEAK : 250°C  
 OVER 230°C : 20~40s  
 PREHEAT : 150~180°C(60~120s)  
 NOTE2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s  
 NOTE3. CO-PLANARITY SHALL BE 0.1 MAX  
 NOTE4. PC BOARD THICKNESS=1.6  
 NOTE5. RECOMMENDED SOLDER THICKNESS=0.15



PACKAGE STYLE  
 NUMBER OF PRODUCTS: 450 PCS / REEL



RECOMMENDED PC BOARD PATTERN

2	BRASS	LEAD:TIN-COPPER ALLOY PLATING CONTACT:GOLD PLATING	3	BRASS	TIN-COPPER ALLOY PLATING
1	PPS	BLACK			
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT		DESCRIPTION OF REVISIONS
DESIGNED		CHECKED		DATE	
APPROVED : NH. NAKATA		13.03.19		DRAWING NO. EDC3-167881-01	
CHECKED : NH. NAKATA		13.03.19		PART NO. GT8E-6P-2H(01)	
DESIGNED : RZ. KANO		13.03.19		CODE NO. CL758-1005-4-01	
DRAWN : RZ. KANO		13.03.19			

DRAWING FOR REFERENCE: This is subject to change without notice  
 05/31/2013

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hirose Electric:](#)

[GT8E-6P-2H\(01\)](#)