



Rating	10A 125V, 6A 250VAC 1/2HP 125V/250V AC 
	10(4)A 125~250Vac 
	20A 14VDC, 10A 28VDC
Contact Resistance	50m ohm Max.
Insulation Resistance	DC 500V 100M ohm Min.
Dielectric Strength	AC 1500V 1 minute
Operation Temperature	-25°C ~ 85°C
Switch Function	4P DPST (ON)-OFF

**MATERIAL:**

Frame: Black, Nylon 66


Actuator: Black, PC

Terminals: Silver plated, Copper alloy


Waterproof Rubber: Black, Silicone

Printed: None






**Mounting Hole**



**Circuit Diagram**



Full travel: 4.5mm



Tolerances ±0.3 Unless Otherwise Specified

10/20/14	黃洋	歐規及UL61058通過,追加刻字10(4)A 125~250Vac, ENEC15			
03/25/13	柳新強	為了改善耳部裝入面板後,內彎容易脫出面板,變更耳部形狀			
05/30/11	曹盈芳	更正圖面尺寸,原20更正為2.0			
Date	Name	Description			No.
Drawn	Checked	Approved	SCI BOM No.	1830627	Model Name PUSH SWITCH
黃洋			Customer No.		Model No. R13-527A2-02-BB
10/20/14	11/13-14	11/14-14	Unit	mm	 Shin Chin Industrial Co., Ltd.
					Rev. 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Shin Chin:](#)

[R13-527A2-02-BB](#)