

Surface Mount Termination
12 Watts, 50Ω



Features:

- RoHS Compliant
- 12 Watts
- DC – 6.0 GHz
- AIN Ceramic
- Non-Nichrome Resistive Element
- Low Return Loss
- 100% Tested
- Small Size

Description:

The C12N50Z4 is a high performance AIN surface mount termination. The termination is well suited to all cellular frequency bands such as; AMPS, GSM, DCS, PCS, PHS and UMTS. The high power handling makes the part ideal for terminating high power 90 degree couplers and for use in microstrip circuits. The termination is also RoHS compliant!

General Specifications:


Resistive Element	Thick film
Substrate	AIN Ceramic
Terminal Finish	Matte Tin over Nickel Barrier
Operating Temperature	-55 to +150°C (see de rating chart)

Electrical Specifications:


Power:	12 Watts
Frequency Range:	DC – 6.0 GHz
Return Loss	>20 dB

Specification based on unit properly installed using suggested mounting instructions and a 50 ohm nominal impedance. **Specifications subject to change.**


Outline Drawing:




Typical Performance:




Power de-rating:



Mounting Footprint:



Tape & Reel:



Contact us:
rf&s_support@ttm.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Anaren:](#)

[C12N50Z4](#)