


KEMET Part Number: PEH506JDE5180M2
(A511EF183M035A)

KEMET
a YAGEO company

PEH506, Aluminum Electrolytic, 18,000 uF, 20%, 35 VDC, -40/+85°C



General Information

Series:	PEH506
Dielectric:	Aluminum Electrolytic
Description:	Snap-In, Aluminum Electrolytic
RoHS:	Yes
Lead:	2 Pin
AEC-Q200:	No
Component Weight:	56 g
Notes:	Add 0.5mm To D And 1mm To L For Sleeving.
Shelf Life:	208 Weeks

Dimensions

D	35mm +/-0.5mm
L	40mm +/-1mm
S	10mm +/-0.1mm
LL	6.3mm +/-1mm
F	2mm +/-0.1mm

Specifications

Capacitance:	18,000 uF
Capacitance Tolerance:	20%
Voltage DC:	35 VDC
Temperature Range:	-40/+85°C
Rated Temperature:	85°C
Life:	3000 Hrs (Rated Voltage And Ripple Current At 85C), 6000 Hrs (Rated Voltage At 85C)
Resistance:	45 mOhms (100Hz 20C), 42 mOhms (100kHz 20C)
Ripple Current:	4.7 Amps (100Hz 85C), 8.9 Amps (20kHz 40C)
Leakage Current:	1890 uA (5min 20°C)

Packaging Specifications

Packaging:	Bulk, Bag
-------------------	-----------

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

KEMET
a YAGEO company

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KEMET:](#)

[A511EF183M035A](#)