

42.5 GHz Surface Mount Bandpass Filter

B424MEZS

COMPLEX • DLI • JOHANSON MFG
NOVACAP • SYFER • VOLTRONICS
www.knowlescapacitors.com

DESCRIPTION

One of DLI's surface mountable catalog bandpass filters designed for the 5G band. This filter utilizes DLI's low loss temperature stable materials which offer small size and minimal performance variation over temperature. The catalog BPF's are offered in a variety of frequency bands, which offers a drop in solution with highly repeatable performance.

FEATURES

- Small Size
- Solder Surface Mount Package
- Moisture Sensitivity Level: MSL1
- Frequency Stable over Temperature
- Operating & Storage Temp: -55°C to +125°C
- Characteristic Impedance: 50Ω


SPECIFICATIONS*

Parameter	Frequency Range (GHz)	Min	Typ.	Max
Insertion Loss (dB)	39.7 - 45.3		1.5	2
Return Loss (dB)		9.5	10	12
Low Side Rejection (dB)	DC - 37	30	40	
High Side Rejection (dB)	47.5 - 60	20	30	
Input Power (W)				TBD
Size (L x W x H)	0.236 x 0.080 x 0.065 in 6.00 x 2.03 x 0.165 mm			

*Electrical specifications based on typical probed performance at room temperature. Insertion loss shall vary ± 0.5 dB over temperature.

** Customer is required to provide shielding for part to ensure proper performance.

Typical Measured Performance



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Knowles:](#)

[B424MEZS-T](#)