

## RZW Series

### Features

- 105°C, 4,000 ~ 10,000 hours assured
- Low ESR, suitable for switching power supplies
- Smaller size with large permissible ripple current
- RoHs Compliance




Sleeve & Marking Color: Black & Golden

### Specifications

Items	Performance																																		
Category Temperature Range	-55°C ~ +105°C																																		
Capacitance Tolerance	±20% (at 120Hz, 20°C)																																		
Leakage Current (at 20°C)	$I = 0.01CV$ or $3 (\mu A)$ whichever is greater (after 2 minutes) Where, C= rated capacitance in $\mu F$ V = rated DC working voltage in V																																		
Tan $\delta$ (at 120 Hz, 20°C)	<table border="1"> <thead> <tr> <th>Rated Voltage</th> <th>6.3</th> <th>10</th> <th>16</th> <th>25</th> <th>35</th> <th>50</th> <th>63</th> </tr> </thead> <tbody> <tr> <td>Tan<math>\delta</math> (max)</td> <td>0.22</td> <td>0.19</td> <td>0.16</td> <td>0.14</td> <td>0.12</td> <td>0.10</td> <td>0.09</td> </tr> </tbody> </table> <p>When the capacitance exceeds 1000<math>\mu F</math>, 0.02 shall be added every 1000<math>\mu F</math> increase.</p>	Rated Voltage	6.3	10	16	25	35	50	63	Tan $\delta$ (max)	0.22	0.19	0.16	0.14	0.12	0.10	0.09																		
Rated Voltage	6.3	10	16	25	35	50	63																												
Tan $\delta$ (max)	0.22	0.19	0.16	0.14	0.12	0.10	0.09																												
Low Temperature Characteristics (at 120Hz)	<p>Impedance ratio shall not exceed the values given in the table below.</p> <table border="1"> <thead> <tr> <th>Rated Voltage</th> <th>6.3</th> <th>10</th> <th>16</th> <th>25</th> <th>35</th> <th>50</th> <th>63</th> </tr> </thead> <tbody> <tr> <td>Impedance Ratio <math>Z(-55^\circ C)/Z(+20^\circ C)</math></td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> <td>3</td> </tr> </tbody> </table>	Rated Voltage	6.3	10	16	25	35	50	63	Impedance Ratio $Z(-55^\circ C)/Z(+20^\circ C)$	3	3	3	3	3	3	3																		
Rated Voltage	6.3	10	16	25	35	50	63																												
Impedance Ratio $Z(-55^\circ C)/Z(+20^\circ C)$	3	3	3	3	3	3	3																												
Endurance	<table border="1"> <thead> <tr> <th rowspan="2">Time</th> <th>6.3 ~ 10V</th> <td>4,000 Hrs for <math>\phi D = 5 \sim 6.3</math> mm; 6,000 Hrs for <math>\phi D = 8 \sim 10</math> mm; 8,000 Hrs for <math>\phi D \geq 12.5</math> mm</td> </tr> <tr> <th>16 ~ 63V</th> <td>5,000 Hrs for <math>\phi D = 5 \sim 6.3</math> mm; 7,000 Hrs for <math>\phi D = 8 \sim 10</math> mm; 10,000 Hrs for <math>\phi D \geq 12.5</math> mm</td> </tr> </thead> <tbody> <tr> <td>Capacitance Change</td> <td colspan="2">Within ±25% of initial value</td> </tr> <tr> <td>Tan<math>\delta</math></td> <td colspan="2">Less than 200% of specified value</td> </tr> <tr> <td>Leakage Current</td> <td colspan="2">Within specified value</td> </tr> </tbody> </table> <p>* The above specifications shall be satisfied when the capacitors are restored to 20°C after the rated voltage applied with rated ripple current for 4,000 ~ 10,000 hours at 105°C.</p>	Time	6.3 ~ 10V	4,000 Hrs for $\phi D = 5 \sim 6.3$ mm; 6,000 Hrs for $\phi D = 8 \sim 10$ mm; 8,000 Hrs for $\phi D \geq 12.5$ mm	16 ~ 63V	5,000 Hrs for $\phi D = 5 \sim 6.3$ mm; 7,000 Hrs for $\phi D = 8 \sim 10$ mm; 10,000 Hrs for $\phi D \geq 12.5$ mm	Capacitance Change	Within ±25% of initial value		Tan $\delta$	Less than 200% of specified value		Leakage Current	Within specified value																					
Time	6.3 ~ 10V		4,000 Hrs for $\phi D = 5 \sim 6.3$ mm; 6,000 Hrs for $\phi D = 8 \sim 10$ mm; 8,000 Hrs for $\phi D \geq 12.5$ mm																																
	16 ~ 63V	5,000 Hrs for $\phi D = 5 \sim 6.3$ mm; 7,000 Hrs for $\phi D = 8 \sim 10$ mm; 10,000 Hrs for $\phi D \geq 12.5$ mm																																	
Capacitance Change	Within ±25% of initial value																																		
Tan $\delta$	Less than 200% of specified value																																		
Leakage Current	Within specified value																																		
Shelf Life Test	<table border="1"> <thead> <tr> <th>Test Time</th> <td>1,000 Hrs</td> </tr> </thead> <tbody> <tr> <td>Capacitance Change</td> <td>Within ±25% of initial value</td> </tr> <tr> <td>Tan<math>\delta</math></td> <td>Less than 200% of specified value</td> </tr> <tr> <td>Leakage Current</td> <td>Within specified value</td> </tr> </tbody> </table> <p>* The above specifications shall be satisfied when the capacitors are restored to 20°C after exposing them for 1,000 hours at 105°C without voltage applied.</p>	Test Time	1,000 Hrs	Capacitance Change	Within ±25% of initial value	Tan $\delta$	Less than 200% of specified value	Leakage Current	Within specified value																										
Test Time	1,000 Hrs																																		
Capacitance Change	Within ±25% of initial value																																		
Tan $\delta$	Less than 200% of specified value																																		
Leakage Current	Within specified value																																		
Ripple Current & Frequency Multipliers	<table border="1"> <thead> <tr> <th rowspan="2">Cap.(<math>\mu F</math>)</th> <th colspan="4">Freq.(Hz)</th> </tr> <tr> <th>120</th> <th>1k</th> <th>10k</th> <th>100k up</th> </tr> </thead> <tbody> <tr> <td>under ~ 33</td> <td>0.42</td> <td>0.70</td> <td>0.90</td> <td>1.0</td> </tr> <tr> <td>39 ~ 270</td> <td>0.50</td> <td>0.73</td> <td>0.92</td> <td>1.0</td> </tr> <tr> <td>330 ~ 680</td> <td>0.55</td> <td>0.77</td> <td>0.94</td> <td>1.0</td> </tr> <tr> <td>820 ~ 1,800</td> <td>0.6</td> <td>0.80</td> <td>0.96</td> <td>1.0</td> </tr> <tr> <td>2,200 ~ 18,000</td> <td>0.7</td> <td>0.85</td> <td>0.98</td> <td>1.0</td> </tr> </tbody> </table>	Cap.( $\mu F$ )	Freq.(Hz)				120	1k	10k	100k up	under ~ 33	0.42	0.70	0.90	1.0	39 ~ 270	0.50	0.73	0.92	1.0	330 ~ 680	0.55	0.77	0.94	1.0	820 ~ 1,800	0.6	0.80	0.96	1.0	2,200 ~ 18,000	0.7	0.85	0.98	1.0
Cap.( $\mu F$ )	Freq.(Hz)																																		
	120	1k	10k	100k up																															
under ~ 33	0.42	0.70	0.90	1.0																															
39 ~ 270	0.50	0.73	0.92	1.0																															
330 ~ 680	0.55	0.77	0.94	1.0																															
820 ~ 1,800	0.6	0.80	0.96	1.0																															
2,200 ~ 18,000	0.7	0.85	0.98	1.0																															

### Diagram of Dimensions




Lead Spacing and Diameter

Unit: mm

$\phi D$	5	6.3	8	10	12.5	16	18
P	2.0	2.5	3.5	5.0	5.0	7.5	7.5
$\phi d$	0.5		0.6			0.8	
$\alpha$	L < 20: 1.5, L $\geq$ 20: 2.0						
$\beta$	0.5						

The case size of 12.5×16, 16×16, 16×20, 18×16, 18×20 and 18×25 are suitable for below diagram:



All product specifications in the catalog are subject to change without notice. (CAT. 2016E1)

Radial

Dimension:  $\phi D \times L$ (mm)

Ripple Current: mA/rms at 100k Hz, 105°C

## Dimension & Permissible Ripple Current

V <sub>DC</sub> Contents $\mu F$	6.3V (0J)				10V (1A)				16V (1C)				25V (1E)			
	$\phi D \times L$	Impedance ( $\Omega$ , Max/100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance ( $\Omega$ , Max/100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance ( $\Omega$ , Max/100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance ( $\Omega$ , Max/100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz
		20°C	-10°C			20°C	-10°C			20°C	-10°C			20°C	-10°C	
47																
56									5×11	0.58	1.16	210				
100					5×11	0.58	1.16	210					6.3×11	0.22	0.44	340
120									6.3×11	0.22	0.44	340				
150	5×11	0.58	1.16	210												
220					6.3×11	0.22	0.44	340	8×11.5	0.11	0.22	640	8×11.5	0.11	0.22	640
330	6.3×11	0.22	0.44	340					8×11.5	0.11	0.22	640	8×15 10×12.5	0.083 0.080	0.166 0.160	840 865
470					8×11.5	0.11	0.22	640	8×15 10×12.5	0.083 0.080	0.166 0.160	840 865	8×20 10×16	0.064 0.060	0.128 0.120	1,050 1,210
680	8×11.5	0.11	0.22	640	8×15 10×12.5	0.083 0.080	0.166 0.160	840 865	8×20 10×16	0.064 0.060	0.128 0.120	1,050 1,210	10×20 12.5×16	0.046 0.049	0.092 0.098	1,400 1,450
820	10×12.5	0.080	0.16	865									10×25	0.042	0.084	1,650
1,000	8×15	0.087	0.174	840	8×20 10×16	0.064 0.060	0.128 0.120	1,050 1,210	10×20 12.5×16	0.046 0.049	0.092 0.098	1,400 1,450	10×30 12.5×20 16×16	0.031 0.035 0.042	0.062 0.070 0.084	1,910 1,900 1,940
1,200	8×20 10×16	0.069 0.060	0.128 0.120	1,050 1,210	10×20	0.046	0.092	1,400	10×25	0.042	0.084	1,650	18×16	0.043	0.086	2,210
1,500	10×20	0.046	0.092	1,400	10×25 12.5×16	0.042 0.049	0.084 0.090	1,650 1,450	10×30 12.5×20 16×16	0.031 0.035 0.042	0.062 0.070 0.084	1,910 1,900 1,940	12.5×25	0.027	0.054	2,230
1,800	12.5×16	0.045	0.090	1,450									12.5×30 16×20	0.024 0.027	0.048 0.054	2,650 2,530
2,200	10×25	0.042	0.084	1,650	10×30 12.5×20 16×16	0.031 0.035 0.042	0.062 0.070 0.084	1,910 1,900 1,940	12.5×25 18×16	0.027 0.043	0.054 0.086	2,230 2,210	12.5×35 18×20	0.020 0.026	0.040 0.052	2,880 2,860
2,700	10×30 16×16	0.031 0.042	0.062 0.084	1,910 1,940	18×16	0.043	0.086	2,210	12.5×30 16×20	0.024 0.027	0.048 0.054	2,650 2,530	12.5×40 16×25	0.017 0.021	0.034 0.042	3,350 2,930
3,300	12.5×20	0.035	0.070	1,900	12.5×25	0.027	0.054	2,230	12.5×35	0.020	0.040	2,880	16×31.5 18×25	0.017 0.019	0.034 0.038	3,450 3,140
3,900	12.5×25 18×16	0.027 0.043	0.054 0.086	2,230 2,210	12.5×30 16×20	0.024 0.027	0.048 0.054	2,650 2,530	12.5×40 16×25 18×20	0.017 0.021 0.026	0.034 0.042 0.052	3,350 2,930 2,860	16×35.5 18×31.5	0.015 0.015	0.030 0.030	3,610 4,170
4,700	12.5×30	0.024	0.048	2,650	12.5×35	0.020	0.040	2,880	16×31.5 18×25	0.017 0.019	0.034 0.038	3,450 3,140	16×40 18×35.5	0.013 0.014	0.026 0.028	4,080 4,220
5,600	12.5×35 16×20	0.020 0.027	0.040 0.054	2,880 2,530	12.5×40 16×25 18×20	0.017 0.021 0.026	0.034 0.042 0.052	3,350 2,930 2,860	16×35.5 18×31.5	0.015 0.015	0.030 0.030	3,610 4,170	18×40	0.012	0.024	4,280
6,800	12.5×40 16×25 18×20	0.017 0.021 0.026	0.034 0.042 0.052	3,350 2,930 2,860	16×31.5 18×25	0.017 0.019	0.034 0.038	3,450 3,140	16×40	0.013	0.026	4,080				
8,200	16×31.5	0.017	0.034	3,450	16×35.5 18×31.5	0.015 0.015	0.030 0.030	3,610 4,170	18×35.5	0.014	0.02	4,220				
10,000	16×35.5 18×25	0.015 0.019	0.030 0.038	3,610 3,140	16×40 18×35.5	0.013 0.014	0.026 0.028	4,080 4,220	18×40	0.012	0.024	4,280				
12,000	16×40 18×31.5	0.013 0.015	0.026 0.030	4,080 4,170	18×40	0.012	0.024	4,280								
15,000	18×35.5	0.014	0.028	4,220												
18,000	18×40	0.012	0.024	4,280												

Radial



Dimension:  $\phi D \times L$ (mm)

Ripple Current: mA/rms at 100k Hz, 105°C

Dimension & Permissible Ripple Current

V <sub>DC</sub> Contents $\mu F$	35V (1V)				50V (1H)				63V (1J)			
	$\phi D \times L$	Impedance ( $\Omega$ , Max/100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance ( $\Omega$ , Max/100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz	$\phi D \times L$	Impedance ( $\Omega$ , Max/100kHz)		Ripple Current (mA/rms, 105°C) 100k Hz
		20°C	-10°C			20°C	-10°C			20°C	-10°C	
3.3					5×11	2.9	5.8	53				
4.7					5×11	2.5	5.0	95				
10					5×11	2.0	4.0	130				
15									5×11	1.2	2.4	165
22					5×11	0.91	1.82	180				
33	5×11	0.58	1.16	210					6.3×11	0.49	0.98	265
56	6.3×11	0.22	0.44	340	6.3×11	0.39	0.78	295	8×11.5	0.31	0.62	500
82									8×15 10×12.5	0.22 0.15	0.44 0.30	665 690
100					8×11.5	0.22	0.44	555				
120					8×15	0.150	0.30	730	8×20 10×16	0.17 0.11	0.34 0.22	820 950
150	8×11.5	0.11	0.22	640	10×12.5	0.160	0.32	760				
180					8×20	0.118	0.236	910	10×20 12.5×16	0.078 0.101	0.156 0.202	1,150 1,150
220	8×15 10×12.5	0.083 0.080	0.166 0.160	840 865	10×16	0.110	0.22	1,050	10×25	0.064	0.128	1,350
270	8×20	0.064	0.128	1,050	10×20 12.5×16	0.078 0.079	0.156 0.158	1,220 1,260	12.5×20	0.057	0.114	1,500
330	10×16	0.060	0.120	1,210	10×25	0.072	0.144	1,440				
390									12.5×25	0.043	0.086	1,900
470	10×20 12.5×16	0.046 0.049	0.092 0.098	1,400 1,450	10×30 12.5×20 16×16	0.056 0.059 0.072	0.112 0.118 0.114	1,690 1,660 1,690	12.5×30 16×20	0.039 0.045	0.078 0.090	2,300 2,000
560	10×25	0.042	0.084	1,650	12.5×25 18×16	0.044 0.070	0.088 0.140	1,950 1,930	12.5×35	0.034	0.068	2,500
680	10×30 12.5×20 16×16	0.031 0.035 0.042	0.062 0.070 0.084	1,910 1,900 1,940	12.5×30	0.039	0.078	2,310	12.5×40 16×25 18×20	0.029 0.035 0.042	0.058 0.070 0.084	2,800 2,600 2,500
820					12.5×35 16×20	0.033 0.044	0.066 0.088	2,510 2,210	16×31.5 18×25	0.029 0.034	0.058 0.068	2,850 2,800
1,000	12.5×25 18×16	0.027 0.043	0.054 0.086	2,230 2,210	12.5×40 16×25 18×20	0.027 0.033 0.047	0.054 0.066 0.094	2,920 2,555 2,490	16×35.5	0.027	0.054	2,900
1,200	12.5×30 16×20	0.024 0.027	0.048 0.054	2,650 2,530	16×31.5 18×25	0.027 0.028	0.054 0.056	3,010 2,740	16×40 18×31.5	0.025 0.028	0.050 0.056	3,400 3,300
1,500	12.5×35	0.020	0.040	2,880	16×35.5	0.024	0.048	3,150	18×35.5	0.025	0.050	3,400
1,800	12.5×40 16×25 18×20	0.017 0.021 0.026	0.034 0.042 0.052	3,350 2,930 2,860	16×40 18×31.5	0.021 0.024	0.042 0.048	3,710 3,635	18×40	0.024	0.048	3,500
2,200	16×31.5 18×25	0.017 0.019	0.034 0.038	3,450 3,140	18×35.5	0.022	0.044	3,680				
2,700	16×35.5 18×31.5	0.015 0.015	0.030 0.030	3,610 4,170	18×40	0.018	0.036	3,800				
3,300	16×40 18×35.5	0.013 0.014	0.026 0.028	4,080 4,220								
3,900	18×40	0.012	0.024	4,280								

Radial

Part Numbering System

RZW series    470 $\mu F$      $\pm 20\%$     16V    Bulk Package    Gas Type    8  $\phi \times 15L$     Pb-free and PET sleeve

**RZW**    **471**    **M**    **1C**    **BK**    -    **0815**

Series    Capacitance    Capacitance Tolerance    Rated Voltage    Lead Configuration & Package    Rubber Type    Case Size    Lead Wire and Sleeve type

Note: For more details, please refer to "Part Numbering System (Radial Type)" on page 11.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lelon:](#)

[RZW182M0JBKF-1316P](#) [RZW221M1EBK-0811P](#) [RZW222M1ABK-1320P](#) [RZW272M0JBK-1616P](#) [RZW331M1CBK-0811P](#) [RZW471M1VBK-1316P](#) [RZW472M1EBK-1640P](#) [RZW681M1ABK-1012P](#)