

SUMMARY

Wires

Low voltage 3



Image is for illustrative purpose only

| | |
|------------------|--------------------------------|
| Series | 1F |
| Termination type | Male crimp |
| IP rating | 67 |
| AWG wire size | 20.00 - 18.00 |
| Cable Ø | 3.80 - 10.70 mm |
| Status | active |
| Matching parts | FGS.1F.303.XLM |

Download

[Request a quote](#)

[Catalog](#)

TECHNICAL DETAILS

Mechanics

| | |
|-------------------|---|
| Shell Style/Model | PH*: Straight receptacle |
| Keying | 3 keys (beta=155, gamma=50, plug: female contacts, receptacle: male contacts) |
| Housing Material | Aluminium (nickel plated [SAE AMS QQ N 290], anthracite color) shell and nut, other pieces bronze/brass |
| Weight | 7.07 g |

Performance

| | |
|---------------|---------------------------|
| Configuration | 1F.303 : 3 Low Voltage |
| Insulator | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 12 Amps |

Specifications

Contact Type: Crimp
Contact Retention: 40 N
Contact Dia.: 1.3 mm (0.051in)
Bucket Dia.: 1.4 mm (0.055in)
Min. Conductor: 0.5 mm² (AWG 20)
Max. Conductor: 1 mm² (AWG 18)
R (max): 3.6 mOhm
Vtest (contact-shell): 1850 V (AC), 2600 V (DC)


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Vtest (contact-contact): 1600 V (AC), 2250 V (DC)

Others

Endurance (Shell): 1000 mating cycles
Temp (min / max): -15°C / +200°C
Humidity (max): <=95% [at 60 deg C / 140 F]
Vibration: 15 g [10 Hz - 2000 Hz]
Shock Resistance: 100 g [6 ms]
Climatical Category: 15/200/21 (Aluminium shell)
Salt Spray Corrosion: max. 48 hr

DRAWINGS



Dimensions

| | A | B | L | X |
|-----|------|------|------|------|
| mm. | 14 | 10.7 | 26.7 | 8 |
| in. | 0,55 | 0,42 | 1,05 | 0,31 |

RECOMMENDED BY LEMO

Tools

Crimp Tool: [DPC.91.701.V](#)

Crimp settings: AWG/Selector = 18-20/8-7

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Positionner: [DCE.91.131.FVC](#)

Extractor: [DCF.93.131.4LT](#)

Replacement contact: FGN.1F.565.ZZC

Cables

| | | | |
|--------------------|---------------|-------|---|
| CMN.03.T18.055PGZE | | Grey |  |
| CMN.03.T18.055PNZE | | |  |
| CMN.03.T18.055QGZE | TPR (medical) | Grey |  |
| CMN.03.T20.049PGZE | | Grey |  |
| CMN.03.T20.049PNZE | | |  |
| 130240 | PVC | Black |  |
| 130250 | PVC | Grey |  |
| 230500 | PVC | Grey |  |
| 230750 | PVC | Grey |  |
| 30110 | PVC | Grey |  |
| 30260 | PVC | Black |  |
| 3220 | PVC | Black |  |
| 3280 | PVC | Black |  |
| 60080 | PVC | Grey | |

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[PHS.1F.303.XLC](#)