

## SUMMARY

### # Wires

Low voltage 14



Image is for illustrative purpose only

|                  |                                   |
|------------------|-----------------------------------|
| Series           | 1P                                |
| Termination type | Female solder                     |
| IP rating        | 50                                |
| AWG wire size    | 0.00 - 0.00                       |
| Cable Ø          | 0.00 - 0.00 mm                    |
| Status           | active                            |
| Matching parts   | <a href="#">PAA.M1.4SL.AC52GZ</a> |

### Download

[Request a quote](#)

[Eplan](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |   |
|-------------------|---|
| Shell Style/Model | PL*: Fixed receptacle, nut fixing                                   |
| Keying            | 2 keys (alpha=40; Plug: male contacts; Receptacle: female contacts) |
| Housing Material  | PEI (Polyetherimide), gray  |
| Variant           | G : Gray front nut  |
| Weight            | 5.72 g  |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | 1P.M14 : 14 Low Voltage   |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 2 Amps                    |

### Specifications

|  |                               |
|--|-------------------------------|
| Contact Type:                          | Solder                        |
| Contact Dia.:                          | 0.5 mm (0.0201in)             |
| Bucket Dia.:                           | 0.45 mm (0.018in)             |
| Max. Solid Conductor:                  | 0.09 mm <sup>2</sup> (AWG 28) |
| Max. Stranded Conductor:               | 0.09 mm <sup>2</sup> (AWG 28) |
| R (max):                               | 8.5 mOhm                      |
| Test voltage (kV rms) Contact-contact: | 0.6                           |


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Air clearance min.: 0.5 mm  
Creepage distance min.: 0.5 mm

## Others

Endurance (Shell): >2000 mating cycles  
Temp (min / max): -50°C / +170°C  
F ret (min): 50 N  
F ret (max): 150 N  
Steam sterilization: > 100 times (with potting on rear connection)

## DRAWINGS



## Dimensions

|     | A    | L    | N    |
|-----|------|------|------|
| mm. | 19.5 | 25   | 20.5 |
| in. | 0,77 | 0,98 | 0,81 |

## RECOMMENDED BY LEMO

## Tools

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

*LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[PLA.M1.4SL.LG](#)