

SUMMARY

Wires

Low voltage 10

Image is for illustrative purpose only

Series SP
Termination type Female solder
IP rating 50
AWG wire size 30.00 - 22.00
Cable Ø 5.30 - 6.50 mm
Status active
Matching parts [SAN.M10.NLA.6GZ](#)

Download

[Request a quote](#)
[Catalog](#)

TECHNICAL DETAILS

Mechanics

Shell Style/Model *:
Keying 3 keys (alpha=0, gamma=30, plug: male contacts, receptacle: female contacts)
Housing Material Proprietary sulfone, black
Variant GZ : Gray collet nut for bend relief

Performance

Configuration SP.M10 : 10 Low V.
Insulator L: PEEK (UL 94 / V-0/1.5)
Rated Current 4.2 Amps

Specifications

Contact Type: Solder
Contact Dia.: 0.7 mm (0.028in)
Bucket Dia.: 0.8 mm (0.032in)
Max. Solid Conductor: 0.36 mm² (AWG 22)
Max. Stranded Conductor: 0.36 mm² (AWG 28)
R (max): 8.5 mOhm
Test voltage (kV rms) Contact-contact: 1.15
Air clearance min.: 0.7 mm
Creepage distance min.: 0.7 mm


LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

Endurance (Shell): >2000 mating cycles

Temp (min / max): -50°C / +170°C

DRAWINGS



RECOMMENDED BY LEMO

Tools

Crimp Tool: [DPC.91.701.V](#)

Cables

CMN.10.T28.053QGZE	TPR (medical)	Grey	
110240	PTFE	White	

110280	PVC	Black	
210140	PVC	Grey	
210260	PVC	Black	

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LEMO:](#)

[SRN.M10.NLL.6GZ](#)