



LED Display

Product Data Sheet

LTD-4708B

Spec No.: DS30-2000-370

Effective Date: 11/14/2000

Revision: -

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

LITE-ON Technology Corp. / Optoelectronics

No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C.

Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660

<http://www.liteon.com/opto>

FEATURES

- * 0.4-INCH (10.0-mm) DIGIT HEIGHT.
- * CONTINUOUS UNIFORM SEGMENTS.
- * LOW POWER REQUIREMENT.
- * EXCELLENT CHARACTERS APPEARANCE.
- * HIGH BRIGHTNESS & HIGH CONTRAST.
- * WIDE VIEWING ANGLE.
- * SOLID STATE RELIABILITY.
- * CATEGORIZED FOR LUMINOUS INTENSITY.
- * LOW POWER REQUIRMENT.


DESCRIPTION

The LTD-4708B is a 0.4-inch (10-mm) digit height dual digit seven-segment display. This device utilizes blue LED chips, which are made from GaN on a SiC substrate, and has a gray face and white segments.

DEVICE


| PART NO. | DESCRIPTION |
|-----------|---|
| BLUE | Duplex Common Cathode Rt. Hand Decimal |
| LTD-4708B | |

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are ± 0.25 -mm (0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



PIN CONNECTION

| No. | CONNECTION |
|------------|--------------------------|
| 1 | ANODE C |
| 2 | ANODE D.P. |
| 3 | ANODE E |
| 4 | COMMON CATHODE (DIGIT 2) |
| 5 | ANODE D |
| 6 | ANODE F |
| 7 | ANODE G |
| 8 | ANODE B |
| 9 | COMMON CATHODE (DIGIT 1) |
| 10 | ANODE A |

ABSOLUTE MAXIMUM RATING AT Ta=25°C

| PARAMETER | MAXIMUM RATING | UNIT |
|--|--|--------------------|
| Power Dissipation Per Segment | 65 | mW |
| Peak Forward Current Per Segment (1/10 Duty Cycle, 0.1ms Pulse Width) | 60 | mA |
| Continuous Forward Current Per Segment | 15 | mA |
| Derating Linear From 25 ⁰ C Per Segment | 0.2 | mA/ ⁰ C |
| Reverse Voltage Per Segment | 5 | V |
| Operating Temperature Range | -35 ⁰ C to +85 ⁰ C | |
| Storage Temperature Range | -35 ⁰ C to +85 ⁰ C | |
| Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at 260 ⁰ C | | |

ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C

| PARAMETER | SYMBOL | MIN. | TYP. | MAX. | UNIT | TEST CONDITION |
|-----------------------------------|-------------------|------|------|------|------|----------------------|
| Average Luminous Intensity | I _v | 1200 | 3600 | | μcd | I _F =10mA |
| Peak Emission Wavelength | λ _p | | 428 | | nm | I _F =20mA |
| Spectral Line Half-Width | Δλ | | 65 | | nm | I _F =20mA |
| Dominant Wavelength | λ _d | | 466 | | nm | I _F =20mA |
| Forward Voltage Per Segment | V _F | | 3.8 | 4.5 | V | I _F =20mA |
| Reverse Current Per Segment | I _R | | | 100 | μA | V _R =5V |
| Luminous Intensity Matching Ratio | I _v -m | | | 2:1 | | I _F =10mA |

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig1. RELATIVE INTENSITY VS. WAVELENGTH




Fig2. RELATIVE LUMINOUS EFFICIENCY
VS. PEAK FORWARD CURRENT
(250us pulse width; 2ms period)




Fig3. FORWARD CURRENT VS.
FORWARD VOLTAGE




Fig4. RELATIVE LUMINOUS INTENSITY
VS. FORWARD CURRENT




Fig5. MAX. ALLOWABLE DC CURRENT
VS. AMBIENT TEMPERATURE.




Fig6. MAX. PEAK CURRENT VS.
DUTY CYCLE %
(REFRESH RATE 1KHz)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lite-On:](#)

[LTD-4708B](#)