

## IGBT (NPT) Module

$$V_{CES} = 1200V$$

$$I_{C25} = 160A$$

$$V_{CE(sat)} = 2.2V$$


Boost Chopper + free wheeling Diode


Part number

MID145-12A3



Backside: isolated

 E72873



### Features / Advantages:

- NPT IGBT technology
- low saturation voltage
- low switching losses
- switching frequency up to 30 kHz
- square RBSOA, no latch up
- high short circuit capability
- positive temperature coefficient for easy parallelling
- MOS input, voltage controlled
- ultra fast free wheeling diodes

### Applications:

- AC motor drives
- Solar inverter
- Medical equipment
- Uninterruptible power supply
- Air-conditioning systems
- Welding equipment
- Switched-mode and resonant-mode power supplies
- Inductive heating, cookers
- Pumps, Fans


### Package: Y4

- Isolation Voltage: 3600 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

| Free Wheeling Diode FWD |  |   |                         | Ratings |      |      |
|-------------------------|--|---|-------------------------|---------|------|------|
| Symbol                  | Definition                                   | Conditions  | min.                    | typ.    | max. | Unit |
| $V_{RSM}$               | max. non-repetitive reverse blocking voltage | $T_{VJ} = 25^{\circ}C$  |                         |         | 1200 | V    |
| $V_{RRM}$               | max. repetitive reverse blocking voltage     | $T_{VJ} = 25^{\circ}C$  |                         |         | 1200 | V    |
| $I_R$                   | reverse current, drain current               | $V_R = 1200 V$  | $T_{VJ} = 25^{\circ}C$  |         | 1    | mA   |
|                         |  | $V_R = 1200 V$  | $T_{VJ} = 125^{\circ}C$ |         | 3    | mA   |
| $V_F$                   | forward voltage drop                         | $I_F = 100 A$   | $T_{VJ} = 25^{\circ}C$  |         | 2.60 | V    |
|                         |  |   |                         |         | 3.10 | V    |
|                         |  | $I_F = 100 A$   | $T_{VJ} = 125^{\circ}C$ |         | 2.00 | V    |
|                         |  |   |                         |         | 2.40 | V    |
| $I_{FAV}$               | average forward current                      | $T_C = 80^{\circ}C$<br>DC current $d = 1$                     | $T_{VJ} = 150^{\circ}C$ |         | 95   | A    |
|                         |  |   |                         |         |      |      |
| $V_{FO}$                | threshold voltage                            | } for power loss calculation only                             | $T_{VJ} = 150^{\circ}C$ |         | 1.30 | V    |
| $r_F$                   | slope resistance                             |   |                         |         | 7.5  | mΩ   |
| $R_{thJC}$              | thermal resistance junction to case          |   |                         |         | 0.18 | K/W  |
| $R_{thCH}$              | thermal resistance case to heatsink          |   |                         | 0.18    |      | K/W  |
| $P_{tot}$               | total power dissipation                      |   | $T_C = 25^{\circ}C$     |         | 700  | W    |
| $I_{FSM}$               | max. forward surge current                   | $t = 10 \text{ ms}; (50 \text{ Hz}), \text{ sine}; V_R = 0 V$ | $T_{VJ} = 45^{\circ}C$  |         | 700  | A    |
| $C_J$                   | junction capacitance                         | $V_R = 600 V \quad f = 1 \text{ MHz}$                         | $T_{VJ} = 25^{\circ}C$  |         | 30   | pF   |




| Boost IGBT            |                                      |  |      | Ratings |          |         |  |
|-----------------------|--------------------------------------|--|------|---------|----------|---------|--|
| Symbol                | Definition                           | Conditions   | min. | typ.    | max.     | Unit    |  |
| $V_{CES}$             | collector emitter voltage            | $T_{VJ} = 25^{\circ}C$   |      |         | 1200     | V       |  |
| $V_{GES}$             | max. DC gate voltage                 |  |      |         | $\pm 20$ | V       |  |
| $V_{GEM}$             | max. transient gate emitter voltage  |  |      |         | $\pm 30$ | V       |  |
| $I_{C25}$             | collector current                    | $T_C = 25^{\circ}C$  |      |         | 160      | A       |  |
| $I_{C80}$             |                                      | $T_C = 80^{\circ}C$  |      |         | 110      | A       |  |
| $P_{tot}$             | total power dissipation              | $T_C = 25^{\circ}C$  |      |         | 700      | W       |  |
| $V_{CE(sat)}$         | collector emitter saturation voltage | $I_C = 100A; V_{GE} = 15V$   |      |         | 2.2      | V       |  |
|                       |                                      |  |      |         | 2.7      | V       |  |
| $V_{GE(th)}$          | gate emitter threshold voltage       | $I_C = 4mA; V_{GE} = V_{CE}$   | 4.5  | 5.5     | 6.5      | V       |  |
| $I_{CES}$             | collector emitter leakage current    | $V_{CE} = V_{CES}; V_{GE} = 0V$  |      |         | 6        | mA      |  |
|                       |                                      |  |      |         | 9        | mA      |  |
| $I_{GES}$             | gate emitter leakage current         | $V_{GE} = \pm 20V$   |      |         | 400      | nA      |  |
| $Q_{G(on)}$           | total gate charge                    | $V_{CE} = 600V; V_{GE} = 15V; I_C = 100A$  |      | 480     |          | nC      |  |
| $t_{d(on)}$           | turn-on delay time                   | inductive load<br>$V_{CE} = 600V; I_C = 100A$<br>$V_{GE} = \pm 15V; R_G = 6.8\Omega$ |      | 100     |          | ns      |  |
| $t_r$                 | current rise time                    |  |      | 60      |          | ns      |  |
| $t_{d(off)}$          | turn-off delay time                  |  |      | 600     |          | ns      |  |
| $t_f$                 | current fall time                    |  |      | 90      |          | ns      |  |
| $E_{on}$              | turn-on energy per pulse             |  |      | 16      |          | mJ      |  |
| $E_{off}$             | turn-off energy per pulse            |  |      | 15      |          | mJ      |  |
| <b>RBSOA</b>          | reverse bias safe operating area     | $V_{GE} = \pm 15V; R_G = 6.8\Omega$  |      |         |          |         |  |
| $I_{CM}$              |                                      | $V_{CEmax} = 1200V$  |      |         | 200      | A       |  |
| <b>SCSOA</b>          | short circuit safe operating area    | $V_{CEmax} = 1200V$  |      |         |          |         |  |
| $t_{SC}$              | short circuit duration               | $V_{CE} = 1200V; V_{GE} = \pm 15V$   |      |         | 10       | $\mu s$ |  |
| $I_{SC}$              | short circuit current                | $R_G = 6.8\Omega; \text{non-repetitive}$   |      | 330     |          | A       |  |
| $R_{thJC}$            | thermal resistance junction to case  |  |      |         | 0.18     | K/W     |  |
| $R_{thCH}$            | thermal resistance case to heatsink  |  |      |         | 0.18     | K/W     |  |
| <b>Boost Diode BD</b> |                                      |  |      |         |          |         |  |
| $V_{RRM}$             | max. repetitive reverse voltage      | $T_{VJ} = 25^{\circ}C$   |      |         | 1200     | V       |  |
| $I_{F25}$             | forward current                      | $T_C = 25^{\circ}C$  |      |         | 150      | A       |  |
| $I_{F80}$             |                                      | $T_C = 80^{\circ}C$  |      |         | 95       | A       |  |
| $V_F$                 | forward voltage                      | $I_F = 100A$   |      |         | 2.60     | V       |  |
|                       |                                      |  |      | 1.90    |          | V       |  |
| $I_R$                 | reverse current                      | $V_R = V_{RRM}$  |      |         | 1        | mA      |  |
|                       |                                      |  |      | 1.5     |          | mA      |  |
| $Q_{rr}$              | reverse recovery charge              | $V_R = 600V$<br>$-di_F/dt = 600A/\mu s$<br>$I_F = 100A; V_{GE} = 0V$                 |      | 8.5     |          | $\mu C$ |  |
| $I_{RM}$              | max. reverse recovery current        |  |      | 62      |          | A       |  |
| $t_{rr}$              | reverse recovery time                |  |      | 200     |          | ns      |  |
| $E_{rec}$             | reverse recovery energy              |  |      | 1.5     |          | mJ      |  |
| $R_{thJC}$            | thermal resistance junction to case  |  |      |         | 0.45     | K/W     |  |
| $R_{thCH}$            | thermal resistance case to heatsink  |  |      |         | 0.45     | K/W     |  |

| Package Y4    |  |                      |                                     | Ratings |      |      |
|---------------|--|----------------------|-------------------------------------|---------|------|------|
| Symbol        | Definition   | Conditions           | min.                                | typ.    | max. | Unit |
| $I_{RMS}$     | RMS current  | per terminal         |                                     |         | 300  | A    |
| $T_{VJ}$      | virtual junction temperature                                 |                      | -40                                 |         | 150  | °C   |
| $T_{op}$      | operation temperature  |                      | -40                                 |         | 125  | °C   |
| $T_{stg}$     | storage temperature  |                      | -40                                 |         | 125  | °C   |
| <b>Weight</b> |  |                      |                                     |         | 108  | g    |
| $M_D$         | mounting torque  |                      | 2.25                                |         | 2.75 | Nm   |
| $M_T$         | terminal torque  |                      | 4.5                                 |         | 5.5  | Nm   |
| $d_{Spp/App}$ | creepage distance on surface   striking distance through air | terminal to terminal | 14.0                                | 10.0    |      | mm   |
| $d_{Spb/Apb}$ |  | terminal to backside | 16.0                                | 16.0    |      | mm   |
| $V_{ISOL}$    | isolation voltage  | t = 1 second         |                                     |         | 3600 | V    |
|               |  | t = 1 minute         | 50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA |         | 3000 | V    |



| Ordering | Part Number | Marking on Product | Delivery Mode | Quantity | Code No. |
|----------|-------------|--------------------|---------------|----------|----------|
| Standard | MID145-12A3 | MID145-12A3        | Box           | 6        | 474215   |

**Outlines Y4**



## Boost IGBT




Fig. 1 Typ. output characteristics




Fig. 2 Typ. output characteristics




Fig. 3 Typ. transfer characteristics




Fig. 4 Typ. turn-on gate charge




Fig. 5 Typ. turn on energy & switching times versus collector current




Fig. 6 Typ. turn off energy & switching times versus collector current




Fig. 12 Typical transient thermal impedance




Fig. 9 Typ. turn on energy & switching times versus gate resistor




Fig. 9 Typ. turn off energy & switching times versus gate resistor

**Boost Diode BD**




Fig. 1 Typ. Forward current vs.  $V_F$




Fig. 2 Typ. peak reverse current  $I_{RM}$  versus  $di/dt$




Fig. 3 Typ. transient thermal impedance junction to case

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IXYS:](#)

[MID145-12A3](#)