

preliminary

# Schottky Diode Gen<sup>2</sup>

$$V_{RRM} = 200\text{ V}$$

$$I_{FAV} = 2 \times 65\text{ A}$$


$$V_F = 0.82\text{ V}$$

High Performance Schottky Diode  
 Low Loss and Soft Recovery  
 Parallel legs


Part number

**DSA120X200LB**

Marking on Product: DSA120X200LB



Backside: isolated

 E72873


### Features / Advantages:

- Very low  $V_f$
- Extremely low switching losses
- Low  $I_{rm}$  values
- Improved thermal behaviour
- High reliability circuit operation
- Low voltage peaks for reduced protection circuits
- Low noise switching

### Applications:

- Rectifiers in switch mode power supplies (SMPS)
- Free wheeling diode in low voltage converters

### Package: SMPD

- Isolation Voltage: 3000 V~
- Industry convenient outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Soldering pins for PCB mounting
- Backside: DCB ceramic
- Reduced weight
- Advanced power cycling

### Disclaimer Notice


Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics).



| Schottky   |  |  |             | Ratings                      |      |      |      |
|------------|--|--|-------------|------------------------------|------|------|------|
| Symbol     | Definition                                   | Conditions                               |             | min.                         | typ. | max. | Unit |
| $V_{RSM}$  | max. non-repetitive reverse blocking voltage |  |             |                              |      | 200  | V    |
| $V_{RRM}$  | max. repetitive reverse blocking voltage     |  |             |                              |      | 200  | V    |
| $I_R$      | reverse current, drain current               | $V_R = 200$ V                            |             | $T_{VJ} = 25^\circ\text{C}$  |      | 1    | mA   |
|            |  | $V_R = 200$ V                            |             | $T_{VJ} = 125^\circ\text{C}$ |      | 5    | mA   |
| $V_F$      | forward voltage drop                         | $I_F = 60$ A                             |             | $T_{VJ} = 25^\circ\text{C}$  |      | 0.98 | V    |
|            |  | $I_F = 120$ A                            |             |                              |      | 1.22 | V    |
|            |  | $I_F = 60$ A                             |             | $T_{VJ} = 150^\circ\text{C}$ |      | 0.82 | V    |
|            |  | $I_F = 120$ A                            |             |                              |      | 1.10 | V    |
| $I_{FAV}$  | average forward current                      | $T_C = 130^\circ\text{C}$<br>rectangular | $d = 0.5$   | $T_{VJ} = 175^\circ\text{C}$ |      | 65   | A    |
| $V_{F0}$   | threshold voltage                            | } for power loss calculation only        |             |                              |      | 0.51 | V    |
| $r_F$      | slope resistance                             |  |             |                              |      | 2.7  | mΩ   |
| $R_{thJC}$ | thermal resistance junction to case          |  |             |                              |      | 0.8  | K/W  |
| $R_{thCH}$ | thermal resistance case to heatsink          |  |             | 0.40                         |      |      | K/W  |
| $P_{tot}$  | total power dissipation                      |  |             | $T_C = 25^\circ\text{C}$     |      | 185  | W    |
| $I_{FSM}$  | max. forward surge current                   | $t = 10$ ms; (50 Hz), sine; $V_R = 0$ V  |             | $T_{VJ} = 45^\circ\text{C}$  |      | 700  | A    |
| $C_J$      | junction capacitance                         | $V_R = 24$ V                             | $f = 1$ MHz | $T_{VJ} = 25^\circ\text{C}$  |      | 394  | pF   |



| Package SMPD   |  | Ratings                             |      |      |      |      |
|----------------|--|-------------------------------------|------|------|------|------|
| Symbol         | Definition   | Conditions                          | min. | typ. | max. | Unit |
| $I_{RMS}$      | RMS current  | per terminal                        |      |      | 100  | A    |
| $T_{VJ}$       | virtual junction temperature                                 |                                     | -55  |      | 175  | °C   |
| $T_{op}$       | operation temperature  |                                     | -55  |      | 150  | °C   |
| $T_{stg}$      | storage temperature  |                                     | -55  |      | 150  | °C   |
| <b>Weight</b>  |  |                                     |      | 8.5  |      | g    |
| $F_C$          | mounting force with clip                                     |                                     | 40   |      | 130  | N    |
| $d_{Spp/ App}$ | creepage distance on surface / striking distance through air | terminal to terminal                | 1.6  |      |      | mm   |
| $d_{Spb/ Apb}$ |  | terminal to backside                | 4.0  |      |      | mm   |
| $V_{ISOL}$     | isolation voltage  | t = 1 second                        | 3000 |      |      | V    |
|                |  | t = 1 minute                        | 2500 |      |      | V    |
|                |  | 50/60 Hz, RMS; $I_{ISOL} \leq 1$ mA |      |      |      |      |



**Part description**


- D = Diode
- S = Schottky Diode
- A = low VF
- 120 = Current Rating [A]
- X = Parallel legs
- 200 = Reverse Voltage [V]
- LB = SMPD-B

| Ordering    | Ordering Number  | Marking on Product | Delivery Mode | Quantity | Code No. |
|-------------|------------------|--------------------|---------------|----------|----------|
| Standard    | DSA120X200LB-TUB | DSA120X200LB       | Tube          | 20       | 524773   |
| Alternative | DSA120X200LB-TRR | DSA120X200LB       | Tape & Reel   | 200      | 523115   |

**Equivalent Circuits for Simulation**

\* on die level

$T_{VJ} = 175$  °C






Schottky

|              |                    |      |    |
|--------------|--------------------|------|----|
| $V_{0 \max}$ | threshold voltage  | 0.51 | V  |
| $R_{0 \max}$ | slope resistance * | 2.7  | mΩ |




**Outlines SMPD**

**A ( 8 : 1 )**



**Notes:**

- 1) protrusion may add 0.2 mm max. on each side
- 2) additional max. 0.05 mm per side by punching misalignment or overlap of dam bar or bending compression
- 3) DCB area 10 to 50  $\mu\text{m}$  convex; position of DCB area in relation to plastic rim:  $\pm 25 \mu\text{m}$  (measured 2 mm from Cu rim)
- 4) terminal plating: 0.2 - 1  $\mu\text{m}$  Ni + 10 - 25  $\mu\text{m}$  Sn (gal v.) cutting edges may be partially free of plating



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[IXYS:](#)

[DSA120X200LB-TRR](#) [DSA120X200LB-TUB](#)