


HiPerFRED²

V_{RRM}	= 2x	400 V
I_{FAV}	=	10 A
t_{rr}	=	45 ns

High Performance Fast Recovery Diode
 Low Loss and Soft Recovery
 Phase leg


Part number

DPG10P400PJ



Backside: isolated

 E72873



Features / Advantages:

- Planar passivated chips
- Very low leakage current
- Very short recovery time
- Improved thermal behaviour
- Very low I_{rm} -values
- Very soft recovery behaviour
- Avalanche voltage rated for reliable operation
- Soft reverse recovery for low EMI/RFI
- Low I_{rm} reduces:
 - Power dissipation within the diode
 - Turn-on loss in the commutating switch

Applications:

- Antiparallel diode for high frequency switching devices
- Antisaturation diode
- Snubber diode
- Free wheeling diode
- Rectifiers in switch mode power supplies (SMPS)
- Uninterruptible power supplies (UPS)

Package: ISOPLUS220

- Isolation Voltage: 3600 V~
- Industry standard outline
- RoHS compliant
- Epoxy meets UL 94V-0
- Soldering pins for PCB mounting
- Backside: DCB ceramic
- Reduced weight
- Advanced power cycling


Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.



Fast Diode				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
V _{RSM}	max. non-repetitive reverse blocking voltage	T _{VJ} = 25°C				400	V
V _{RRM}	max. repetitive reverse blocking voltage	T _{VJ} = 25°C				400	V
I _R	reverse current, drain current	V _R = 400 V	T _{VJ} = 25°C			1	μA
		V _R = 400 V	T _{VJ} = 150°C			0.18	mA
V _F	forward voltage drop	I _F = 10 A	T _{VJ} = 25°C			1.28	V
		I _F = 20 A				1.48	V
		I _F = 10 A	T _{VJ} = 150°C			1.02	V
		I _F = 20 A				1.24	V
I _{FAV}	average forward current	T _C = 145°C rectangular d = 0.5	T _{VJ} = 175°C			10	A
V _{F0}	threshold voltage	} for power loss calculation only		T _{VJ} = 175°C		0.78	V
r _F	slope resistance					19.4	mΩ
R _{thJC}	thermal resistance junction to case					2.5	K/W
R _{thCH}	thermal resistance case to heatsink				0.5		K/W
P _{tot}	total power dissipation	T _C = 25°C				60	W
I _{FSM}	max. forward surge current	t = 10 ms; (50 Hz), sine; V _R = 0 V		T _{VJ} = 45°C		130	A
C _J	junction capacitance	V _R = 200 V f = 1 MHz		T _{VJ} = 25°C	16		pF
I _{RM}	max. reverse recovery current	} I _F = 15 A; V _R = 270 V -di _F /dt = 200 A/μs		T _{VJ} = 25 °C	4		A
t _{rr}	reverse recovery time			T _{VJ} = 125 °C	5.5		A
				T _{VJ} = 25 °C	45		ns
				T _{VJ} = 125 °C	70		ns

Package ISOPLUS220				Ratings			
Symbol	Definition	Conditions		min.	typ.	max.	Unit
I _{RMS}	RMS current	per terminal				35	A
T _{VJ}	virtual junction temperature			-55		175	°C
T _{op}	operation temperature			-55		150	°C
T _{stg}	storage temperature			-55		150	°C
Weight					2		g
F _C	mounting force with clip			20		60	N
d _{Spp/App}	creepage distance on surface striking distance through air	terminal to terminal		1.0			mm
d _{Spb/Apb}		terminal to backside		3.0			mm
V _{ISOL}	isolation voltage	t = 1 second	50/60 Hz, RMS; I _{ISOL} ≤ 1 mA	3600			V
		t = 1 minute		3000			V



Part description


D = Diode
 P = HiPerFRED
 G = extreme fast
 10 = Current Rating [A]
 P = Phase leg
 400 = Reverse Voltage [V]
 PJ = ISOPLUS220AB (3)

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	DPG10P400PJ	DPG10P400PJ	Tube	50	507202

Equivalent Circuits for Simulation

* on die level

$T_{VJ} = 175^{\circ}\text{C}$



Fast Diode

$V_{0\max}$ threshold voltage


0.78

V

$R_{0\max}$ slope resistance *

16.2


mΩ

Outlines ISOPLUS220


Dim.	Millimeters		Inches	
	min	max	min	max
A	4.00	5.00	0.157	0.197
A1	2.50	3.00	0.098	0.118
A2	1.60	1.80	0.063	0.071
b	0.90	1.30	0.035	0.051
b2	2.35	2.55	0.093	0.100
b4	1.25	1.65	0.049	0.065
c	0.70	1.00	0.028	0.039
D	15.00	16.00	0.591	0.630
D1	12.00	13.00	0.472	0.512
D2	1.10	1.50	0.043	0.059
D3	14.90	15.50	0.587	0.610
E	10.00	11.00	0.394	0.433
E1	7.50	8.50	0.295	0.335
e	2.54 BSC		0.100 BSC	
L	13.00	14.50	0.512	0.571
L1	3.00	3.50	0.118	0.138
T°	42.5	47.5		
W	-	0.1	-	0.004

Die konvexe Form des Substrates ist typ. < 0.04 mm über der Kunststoffoberfläche der Bauteilunterseite
 The convex bow of substrate is typ. < 0.04 mm over plastic surface level of device bottom side

Die Gehäuseabmessungen entsprechen dem Typ TO-273 gemäß JEDEC außer D und D1.
 This drawing will meet all dimensions requirement of JEDEC outline TO-273 except D and D1.




Fast Diode


Fig. 1 Forward current I_F versus V_F




Fig. 2 Typ. reverse recov. charge Q_{rr} versus $-di_F/dt$




Fig. 3 Typ. peak reverse current I_{RM} versus $-di_F/dt$




Fig. 4 Typ. dynamic parameters Q_{rr} , I_{RM} versus T_{VJ}




Fig. 5 Typ. recovery time t_{rr} versus $-di_F/dt$




Fig. 6 Typ. peak forward voltage V_{FR} and t_{fr} versus di_F/dt




Fig. 7 Typ. recovery energy E_{rec} versus $-di_F/dt$




Fig. 8 Transient thermal resistance junction to case