

Features

- AEC-Q101 Qualified
- High breakdown voltage to 1200V for improved reliability
- Maximum Junction Temperature 150°C
- Positive Temperature Coefficient
- Halogen Free. "Green" Device (Note 1)
- Epoxy Meets UL 94 V-0 Flammability Rating
- Lead Free Finish/RoHS Compliant (Note 2) ("P" Suffix
- Designates RoHS Compliant. See Ordering Information)

Applications

- PTC heater



Maximum Ratings

Parameter	Symbol	Rating	Unit
Collector-Emitter Voltage	V_{CE}	1200	V
DC Collector Current, Limited by T_{Jmax}	I_C	145 (Note 3)	A
		80	
Pulsed Collector Current (Note 4)	$I_{C,pluse}$	240	A
Turn off Safe Operating Area $V_{CE} \leq 1200V, T_J \leq 150^\circ C$		240	A
Continuous Gate-Emitter Voltage	V_{GE}	± 20	V
Transient Gate-Emitter Voltage (Note 5)		± 30	
Power Dissipation	P_D	735	W
		294	

Note:

1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
2. High Temperature Solder Exemptions Applied, see EU Directive Annex 7a.
3. Bond wire current limit is 80A.
4. $V_{GE}=15V$, T_p limited by T_{Jmax} .
5. $T_p \leq 10\mu s, D < 0.010$.


Internal Structure



Device Code: MIS80N120NT1Y
Date & Trace Code : QYYWWXXX

Trench and Field Stop IGBT 1200V 80A

STO-220



DIMENSIONS					
DIM	INCHES		mm		NOTE
	MIN	MAX	MIN	MAX	
A	0.171	0.187	4.34	4.74	
A1	0.028	0.039	0.70	1.00	
A2	0.098	0.118	2.50	3.00	
b	0.028	0.051	0.70	1.30	
b1	0.049	0.065	1.25	1.65	
b2	0.049	0.065	1.25	1.65	
b3	0.085	0.093	2.16	2.36	
c	0.028	0.039	0.70	1.00	
D	0.551	0.591	14.00	15.00	
D1	0.492	0.531	12.50	13.50	
D2	0.415	0.454	10.54	11.54	
E	0.394	0.433	10.00	11.00	
E1	0.315	0.354	8.00	9.00	
E2	0.303	0.343	7.70	8.70	
e1	0.100		2.55		TYP.
e2	0.193	0.209	4.90	5.30	
L	0.512	0.571	13.00	14.50	
L1	0.104	0.124	2.65	3.15	
L2	0.020	0.059	0.50	1.50	
L3	0.108	0.128	2.75	3.25	
L4	-	0.059	-	1.50	
θ	42.50°	47.50°	42.50°	47.50°	

Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
IGBT Static Characteristics						
Collector-Emitter Breakdown Voltage	$V_{(BR)CES}$	$V_{GE}=0V, I_C=250\mu A$	1200			V
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$V_{GE}=15V, I_C=33A, T_J=25^\circ C$		1.35	1.65	V
		$V_{GE}=15V, I_C=33A, T_J=125^\circ C$		1.48		
		$V_{GE}=15V, I_C=33A, T_J=150^\circ C$		1.55		
		$V_{GE}=15V, I_C=80A, T_J=25^\circ C$		1.75	2.3	
		$V_{GE}=15V, I_C=80A, T_J=125^\circ C$		2.15		
		$V_{GE}=15V, I_C=80A, T_J=150^\circ C$		2.25		
G-E Threshold Voltage	$V_{GE(th)}$	$I_C=2.60mA, V_{CE}=V_{GE}$	5.35	6.0	6.7	V
C-E Leakage Current	I_{CES}	$V_{CE}=1200V, V_{GE}=0V, T_J=25^\circ C$			0.25	mA
		$V_{CE}=1200V, V_{GE}=0V, T_J=150^\circ C$			1.00	
G-E Leakage Current	I_{GES}	$V_{CE}=0V, V_{GE}=\pm 20V$			100	nA
Dynamic Characteristics						
Input Capacitance	C_{ies}	$V_{CE}=25V, V_{GE}=0V, f=1MHz$		7.94		nF
Reverse Transfer Capacitance	C_{res}			0.19		
Gate Charge	Q_g	$V_{CC}=960V, I_C=80A, V_{GE}=15V$		0.65		μC

Electrical Characteristics @ 25°C (Unless Otherwise Specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
IGBT Switching Characteristics						
Turn-On Delay Time	$t_{d(on)}$	$V_{CC}=600V, I_C=80A,$ $V_{GE}=-5V/+15V, R_G=10\Omega, T_J=25^\circ C$ Inductive Load		33		ns
Rise Time	t_r			85		
Turn-Off Delay Time	$t_{d(off)}$			231		
Fall Time	t_f			174		
Turn-On Energy	E_{on}			7.5		mJ
Turn-Off Energy	E_{off}			4.6		
Turn-On Delay Time	$t_{d(on)}$	$V_{CC}=600V, I_C=80A,$ $V_{GE}=-5V/+15V, R_G=10\Omega, T_J=125^\circ C$ Inductive Load		30		ns
Rise Time	t_r			79		
Turn-Off Delay Time	$t_{d(off)}$			243		
Fall Time	t_f			263		
Turn-On Energy	E_{on}			7.8		mJ
Turn-Off Energy	E_{off}			5.5		
Turn-On Delay Time	$t_{d(on)}$	$V_{CC}=600V, I_C=80A,$ $V_{GE}=-5V/+15V, R_G=10\Omega, T_J=150^\circ C$ Inductive Load		28		ns
Rise Time	t_r			74		
Turn-Off Delay Time	$t_{d(off)}$			252		
Fall Time	t_f			325		
Turn-On Energy	E_{on}			8.0		mJ
Turn-Off Energy	E_{off}			6.2		

Parameter	Symbol	Min	Typ	Max	Units
Operating Junction Temperature Range	T_J	-40		150	$^\circ C$
Storage Temperature Range	T_{stg}	-55		150	$^\circ C$
Thermal Resistance from Junction to Case (IGBT)	$R_{th_{J-C}}$			0.17	$^\circ C/W$
Thermal Resistance from Junction to Ambient	$R_{th_{J-A}}$			62	$^\circ C/W$

Curve Characteristics

Fig. 1 - Typical Output Characteristic($T_J=25^\circ\text{C}$)




Fig. 2 - Typical Output Characteristic ($T_J=150^\circ\text{C}$)




Fig. 3 - Typical Transfer Characteristic




Fig. 4- Capacitance Characteristics




Fig. 7 - IGBT Switching Loss vs. I_C





Fig. 8- IGBT Switching Loss vs. R_g



Curve Characteristics

Fig. 7- Switching Times vs. Collect Current




Fig. 8 - Switching Times vs Gate Resistance




Fig. 9- $V_{GE(th)}$ vs. Junction Temperature




Fig. 10 -FBSOA




Fig. 11 - Collector Current vs. Case Temperature






Fig. 12 - Power Derating



Curve Characteristics

Fig.13 -IGBT Transient Thermal Impedance



Ordering Information

Device	Packing
Part Number-BP	Bulk:50pcs/Tube, 1Kpcs/Box, 5Kpcs/Carton

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes . **Micro Commercial Components Corp** . does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp** . and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Micro Commercial Components \(MCC\):](#)

[MIS80N120NT1YHE3-BP](#)