


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0009484108](#)  
**Status:** **Active**  
**Overview:** [KK Interconnect Solutions](#)  
**Description:** KK 396 PC Board Connector, Top Entry, Polyester Connector, 5.00µm Tin (Sn), 10 Circuits

**Documents:**

|                                |  |
|--------------------------------|--|
| <a href="#">Drawing (PDF)</a>  | <a href="#">Product Specification PS-08-50-001 (PDF)</a>       |
| <a href="#">3D Model</a>       | <a href="#">Packaging Specification PK-41815-001-000 (PDF)</a> |
| <a href="#">3D Model (PDF)</a> | <a href="#">Symbol Footprint Data SYM-09-48-4108-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |



**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |   |
|----------------|---|
| Product Family | PCB Receptacles                           |
| Series         | <a href="#">41815</a>                     |
| Application    | Board-to-Board, Power                     |
| Overview       | <a href="#">KK Interconnect Solutions</a> |
| Product Name   | KK 396                                    |
| UPC            | 800754247184                              |

**Physical**

|                                |                           |
|--------------------------------|---------------------------|
| Circuits (Loaded)              | 10                        |
| Circuits (maximum)             | 10                        |
| Color - Resin                  | Natural                   |
| Flammability                   | 94V-0                     |
| Glow-Wire Capable              | No                        |
| Lock to Mating Part            | Yes                       |
| Material - Metal               | Phosphor Bronze           |
| Material - Plating Mating      | Tin                       |
| Material - Plating Termination | Tin                       |
| Material - Resin               | Polyester                 |
| Net Weight                     | 3.347/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Vertical                  |
| PC Tail Length                 | 3.05mm                    |
| PCB Locator                    | No                        |
| PCB Retention                  | None                      |
| PCB Thickness - Recommended    | 0.80mm                    |
| Packaging Type                 | Tray                      |
| Pitch - Mating Interface       | 3.96mm                    |
| Plating min - Mating           | 5.080µm                   |
| Plating min - Termination      | 5.080µm                   |
| Polarized to PCB               | No                        |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface: Style   | Through Hole              |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 5.0A |
| Voltage - Maximum             | 250V |

**Solder Process Data**

|  |      |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-free Process Capability                   | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[41815 Series](#)

**Mates With**

KK 396 Header [41771](#) , [41772](#) , [41791](#) ,  
[41792](#) , [42491](#) , [42492](#) , [42891](#) , [41661](#) ,  
[41662](#) , [41671](#) , [41672](#) , [41681](#)

|                                    |                    |
|------------------------------------|--------------------|
| Process Temperature max. C         | 235                |
| <b>Material Info</b>               |                    |
| Engineering Number                 | A-41815-0066       |
| <b>Reference - Drawing Numbers</b> |                    |
| Packaging Specification            | PK-41815-001-000   |
| Product Specification              | PS-08-50-001       |
| Sales Drawing                      | SDA-41815-000      |
| Symbol/Footprint Data              | SYM-09-48-4108-001 |

This document was generated on 09/28/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[09-48-4108](#)