

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0015446806](#)  
**Status:** **Active**  
**Overview:** [C-Grid Connector Products](#)  
**Description:** 2.54mm Pitch C-Grid Receptacle, Through Hole, Dual Row, High Profile, Vertical, High-Temperature, 6 Circuits

**Documents:**

|                                |   |
|--------------------------------|---|
| <a href="#">3D Model</a>       | <a href="#">Product Specification PS-70181-001 (PDF)</a>        |
| <a href="#">3D Model (PDF)</a> | <a href="#">Packaging Specification PK-70873-0660-001 (PDF)</a> |
| <a href="#">Drawing (PDF)</a>  | <a href="#">RoHS Certificate of Compliance (PDF)</a>            |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |   |
|----------------|---|
| Product Family | PCB Receptacles                           |
| Series         | <a href="#">71850</a>                     |
| Application    | Board-to-Board, Signal                    |
| Overview       | <a href="#">C-Grid Connector Products</a> |
| Product Name   | C-Grid                                    |
| UPC            | 800754226554                              |

**Physical**

|                                |                                |
|--------------------------------|--------------------------------|
| Circuits (Loaded)              | 6                              |
| Circuits (maximum)             | 6                              |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 25                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Capable              | No                             |
| Material - Metal               | Phosphor Bronze                |
| Material - Plating Mating      | Tin                            |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Net Weight                     | 0.507/g                        |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| PC Tail Length                 | 3.05mm                         |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness - Recommended    | 1.57mm                         |
| Packaging Type                 | Tray                           |
| Pitch - Mating Interface       | 2.54mm                         |
| Plating min - Mating           | 3.810µm                        |
| Plating min - Termination      | 3.810µm                        |
| Polarized to PCB               | No                             |
| Temperature Range - Operating  | -40° to +105°C                 |
| Termination Interface: Style   | Through Hole                   |


**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 2.5A |
| Voltage - Maximum             | 250V |

**Solder Process Data**

|                              |          |
|------------------------------|----------|
| Lead-free Process Capability | SMC&WAVE |
| Process Temperature max. C   | 260      |

**Material Info**



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[71850 Series](#)

**Mates With**

C-Grid Breakaway Vertical Header [70287](#)  
, [71308](#) , [70280](#) <br> C-Grid Breakaway  
Right-Angle Header [71764](#) , [70216](#) <br> C-  
Grid Vertical Headers [70246](#) , [70567](#) , [70568](#)  
<br> C-Grid Right-Angle Headers [70247](#) ,  
[70229](#) , [74162](#)

Engineering Number

A718500066

**Reference - Drawing Numbers**

Packaging Specification

PK-70873-0660-001

Product Specification

PS-70181-001

Sales Drawing

SDA-71850-0XXX-001

This document was generated on 09/13/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15-44-6806](#)