

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0022112132](#)  
**Status:** **Active**  
**Overview:** [KK® Interconnect System - Molex](#)  
**Description:** KK 254 Solid Header, Vertical, with Friction Lock, 13 Circuits, Gold (Au) Plating

**Documents:**

|  |  |
|--|--|
| <a href="#">Drawing (PDF)</a>                            | <a href="#">Packaging Specification PK-6373-001-000 (PDF)</a>  |
| <a href="#">3D Model</a>                                 | <a href="#">Symbol Footprint Data SYM-22-23-2131-001 (PDF)</a> |
| <a href="#">3D Model (PDF)</a>                           | <a href="#">RoHS Certificate of Compliance (PDF)</a>           |
| <a href="#">Product Specification PS-10-07-001 (PDF)</a> |  |

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**


|                |   |
|----------------|---|
| Product Family | PCB Headers                                     |
| Series         | <a href="#">6373</a>                            |
| Application    | Signal, Wire-to-Board                           |
| Overview       | <a href="#">KK® Interconnect System - Molex</a> |
| Product Name   | KK 254  |
| UPC            | 800753625341                                    |

**Physical**

|                                |                           |
|--------------------------------|---------------------------|
| Breakaway                      | No                        |
| Circuits (Loaded)              | 13                        |
| Circuits (maximum)             | 13                        |
| Color - Resin                  | Natural (White)           |
| Durability (mating cycles max) | 50                        |
| First Mate / Last Break        | No                        |
| Flammability                   | 94V-0                     |
| Glow-Wire Capable              | No                        |
| Guide to Mating Part           | No                        |
| Lock to Mating Part            | Yes                       |
| Material - Metal               | Brass                     |
| Material - Plating Mating      | Gold                      |
| Material - Resin               | Nylon                     |
| Net Weight                     | 1.487/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Vertical                  |
| PC Tail Length                 | 3.56mm                    |
| PCB Locator                    | No                        |
| PCB Retention                  | None                      |
| PCB Thickness - Recommended    | 1.60mm                    |
| Packaging Type                 | Bag                       |
| Pitch - Mating Interface       | 2.54mm                    |
| Pitch - Termination Interface  | 2.54mm                    |
| Polarized to Mating Part       | Yes                       |
| Polarized to PCB               | No                        |
| Shrouded                       | Partial                   |
| Stackable                      | No                        |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface: Style   | Through Hole              |

**Electrical**

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 4.0A |
| Voltage - Maximum             | 500V |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[6373 Series](#)

**Mates With**

[2695](#) , [6471](#) , [7880](#) , [4455](#) , [7720](#)

**Solder Process Data**

|  |      |
|--|------|
| Duration at Max. Process Temperature (seconds) | 005  |
| Lead-free Process Capability                   | WAVE |
| Max. Cycles at Max. Process Temperature        | 001  |
| Process Temperature max. C                     | 235  |

**Material Info**

|                    |               |
|--------------------|---------------|
| Engineering Number | A-6373-13A241 |
|--------------------|---------------|

**Reference - Drawing Numbers**

|                         |                                  |
|-------------------------|----------------------------------|
| Packaging Specification | PK-6373-001-000                  |
| Product Specification   | PS-10-07-001                     |
| Sales Drawing           | SD-6373-001-000, SD-6373-001-002 |
| Symbol/Footprint Data   | SYM-22-23-2131-001               |

This document was generated on 01/03/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-11-2132](#)