

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022284270

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK 254 Breakaway Header, Vertical, 27 Circuits, Tin (Sn) Plating, Mating Pin Length 6.09mm

Documents:

3D Model

Product Specification PS-10-07-001 (PDF)

3D Model (PDF)

Packaging Specification PK-40873-0041-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

42375

Application

Board-to-Board, Signal, Wire-to-Board

Overview

KK Interconnect Solutions

Product Name

KK 254

UPC

800753836075

Physical

Breakaway

Yes

Circuits (Loaded)

27

Circuits (maximum)

27

Color - Resin

Black

Durability (mating cycles max)

25

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Capable

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Plating Mating

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

1.818/g

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.18mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

No

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole


Electrical

Current - Maximum per Contact

4.0A

Voltage - Maximum

500V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free
Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

42375 Series

Mates With

KK Crimp Housing [2695](#) , [6471](#) , [7880](#) , KK
PC Board Connector [4455](#)

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Engineering Number	42375-0027
--------------------	------------

Reference - Drawing Numbers

Packaging Specification	PK-40873-0041-001
Product Specification	PS-10-07-001
Sales Drawing	SD-42375-001-001, SD-42375-001-002

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

22-28-4270