


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0026482196](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 396 Breakaway Header, Right-Angle with Friction Lock, 19 Circuits, Gold (Au) Plating

Documents:

3D Model	Packaging Specification PK-41672-001-001 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-41672-0018-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-08-50-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

Application tooling part link

Application Tooling Part Link	11-20-0901
-------------------------------	------------

General

Product Family	PCB Headers
Series	41672
Application	Power, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 396
UPC	800754904339

Physical

Breakaway	Yes
Circuits (Loaded)	19
Circuits (maximum)	19
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Polyester
Net Weight	7.849/g
Number of Rows	1
Orientation	Right Angle
PC Tail Length	5.38mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Polarized to Mating Part	No
Polarized to PCB	Yes
Shrouded	No
Stackable	No
Temperature Range - Operating	See Product Specification
Termination Interface: Style	Through Hole

Electrical

EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[41672](#) Series

Mates With

[2139](#) KK Crimp Housing, [41695](#) KK Crimp Housing, [6442](#) KK Crimp Housing, [2145](#) PCB Connector, [41815](#) PCB Connector, [3069](#) KK Crimp Housing

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V
Solder Process Data	
Lead-freeProcess Capability	WAVE
Material Info	
Engineering Number	A-41672-A19A241
Reference - Drawing Numbers	
Packaging Specification	PK-41672-001-001
Product Specification	PS-08-50-001
Sales Drawing	SD-41672-001-001
Symbol/Footprint Data	SYM-41672-0018-001

This document was generated on 11/24/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-48-2196](#)