

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0134220011](#)  
**Status:** **Active**  
**Overview:** [Asset Tracking Solutions](#)  
**Description:** Alien Enterprise 4-port Fixed RFID Reader, 916-928 MHz, for Uruguay and Peru

**Documents:**

[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	RFID Products
Series	<a href="#">13422</a>
Comments	Includes Reader ONLY. No PoE/DC Power Supply Included.
Component Type	Fixed RFID Reader
Kit Option	Reader Only
LAN Protocols	TCP/IP,NTP,DNS,DHCP,SNMP
Market	Peru, Uruguay
More Detailed Tech Information	For detailed product and compliance certification information, please <a href="https://www.alientechnology.com/download/alr-f800-documents/?wpdmdl=7608&ind=QUxSLUY4MDAgKDIwMTktMDEtMjM0LmR2eS5wiew Alien Datasheet</a>.
Overview	<a href="#">Asset Tracking Solutions</a>
Product Name	Alien
RFID Standard	EPC C1 Gen 2,ISO 18000-6c
Reader Protocols	ARP,LLRP
Type	Enterprise
UPC	193264422005

**Physical**

Additional Readers Supported	None
Antennas	Up to 4 Supported
Communications	LAN TCP/IP (RJ-45), RS-232 (DB-9 F), USB Console, USB Host
Dimensions	202.00 x 191.00 x 28.00mm
General Purpose I/O	4 in / 8 out (Isolated)
Memory	512 MB RAM,2 GB Flash
Operating System	Linux
Packaging Type	Carton
Software SDK	Java,.NET,Ruby APIs
Temperature Range - Operating	-20° to +50°C

**Electrical**

Frequency	916-928 MHz
Max Conductive RF Power (dBm)	31.6
Power Source	PoE,AC/DC Power Converter

**Material Info**

Engineering Number	F800-URY-RDR-ONLY
--------------------	-------------------



Series image - Reference only

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[13422 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[13422-0011](#)