


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190060003**
Status: **Active**
Overview: Standard Quick-Disconnect Terminals
Description: Flag Avikrimp Quick Disconnect, Female, for 18-22 (0.80-0.35mm²) Wire, Mylar Tape, Tab 6.35 x 0.81mm

Documents:

3D Model	Product Specification PS-19902-014-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-015-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19902-011-001 (PDF)	



Agency Certification

CSA	LR18689
UL	E79133

General

Product Family	Quick Disconnects
Series	<u>19006</u>
Crimp Quality Equipment	Yes
Insulated	Fully
Overview	<u>Standard Quick-Disconnect Terminals</u>
Product Name	Avikrimp
Type	Quick Disconnect
UPC	800753030923

Physical

Barrel Type	Closed
Color - Resin	Red
Flammability	94V-2
Gender	Female
Glow-Wire Capable	Yes
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	1.369/g
Orientation	Flag
Packaging Type	Adhesive Tape on Reel
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Temperature Range - Operating	-65° to +105°C
Wire Insulation Diameter	3.81mm max.
Wire Size AWG	18, 20, 22

Electrical

Voltage - Maximum	600V
-------------------	------

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Engineering Number	AA-5220T
--------------------	----------

Reference - Drawing Numbers

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contained Per -
D(2021)4569-DC (8
July 2021)
Phenol, 2-(2H-
benzotriazol-2-yl)-4,6-
bis(1,1-dim
Ammonium-
pentadecafluorooctanoate
1,3-Propanesultone
4,4'-methylenedi-o-
toluidine
1,2-diethoxyethane
1,2-
Benzenedicarboxylic
acid, bis(3-
methylbutyl)
Disodium 3,3'-[[1,1'-
Biphenyl]-4,4'-
Diylbis(Azo)
Octamethylcyclotetrasiloxane
Dodecamethylcyclohexasiloxane
heptacosafuorotetradecanoic
acid
Octanoic acid,
2,2,3,3,4,4,5,5,6,6,7,7,8,8-
pen
tricosafuorododecanoic
acid
Benzo(ghi)perylene
Dipentyl phthalate
nitrobenzene
Imidazolidine-2-thione
o-toluidine
Dinoseb
Phenanthrene
Dihexyl-phthalate
Dicyclohexyl-
phthalate
propylene oxide

China RoHS

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-014-001,
PS-19902-015-001
SD-19006-001-001

N,N-Dimethylformamide
diethyl sulphate
4-aminoazobenzene
1,3,5-tris-[(2S and 2R)-2,3-epoxypropyl]-1,3,5-t
Perfluorohexane-1-sulphonic acid and its salts
Cadmium sulphate
hexahydro-2-benzofuran-1,3-dione
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
Dioctyltin dilaurate, stannane, dioctyl-, bis(co
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o
Chrysene
Cadmium nitrate
Benz[a]anthracene
Perfluorobutane sulfonic acid (PFBS) and its sal
Tris(4-nonylphenyl, branched and linear) phosphi
Nonadecafluorodecanoic acid (PFDA) and its sodiu
4-Heptylphenol, branched and linear
4-(1,1,3,3-tetramethylbutyl)phenol, ethoxylated
Acids generated from chromium trioxide and their
Zirconia
Aluminosilicate
Refractory Ceramic Fibr
Aluminosilicate
Refractory Ceramic Fibres
Boric acid
n-pentyl-isopentylphthalate
diisohexyl phthalate
Terphenyl, hydrogenated
2-(2H-Benzotriazol-2-yl)-4-(tert-butyl)-6-(sec-b
2-(2H-Benzotriazol-2-yl)-4,6-ditertpentylphenol
2-ethylhexyl 10-ethyl-4,4-dioctyl-7-oxo-8-oxa-3, Disodium-octaborate

2,4-Di-tert-butyl-6-(5-chlorobenzotriazol-2-yl)p
Silicic acid (H₂Si₂O₅),
barium salt (1:1),
lead-
Lead-dipicrate
Potassium
hydroxyoctaoxidizincatedichromate
bis(2-methoxyethyl)
ether
1,2-
Benzenedicarboxylic
acid, di-C₆-8-
branched a
1,2,3-
Trichloropropane
Strontium-chromate
2-Ethoxyethyl acetate
2-Ethoxyethanol
Boric acid, disodium
salt, hydrate
Sodium-chromate
Acrylamide
Tris(2-chloroethyl)
phosphate
Pitch, coal tar, high-
temp.
Lead chromate
molybdate sulfate red
Anthracene oil,
anthracene-low;
Anthracene Oil F
Anthracene oil,
anthracene paste,
distn. lights;
Anthracene oil,
anthracene paste,
anthracene fra
Anthracene oil,
anthracene paste;
Anthracene Oil
Anthracene oil;
Anthracene oil
Arsenic acid
(H₃AsO₄), lead(2+)
salt (1:1)
Bis(tributyltin) oxide
Alkanes, C₁₀-13,
chloro
Di-(2-
ethylhexyl)phthalat
5-tert-Butyl-2,4,6-
trinitro-m-xylene
Cobalt-dichloride
4,4'-
diaminodiphenylmethane
Sulfurous Acid, Lead
Salt, Dibasic
Cadmium Hydroxide
Cyanamide, lead(2+)
salt (1:1)
Borate(1-),
tetrafluoro-, lead (2+)

Lead titanium
zirconium oxide
Lead-titanium-trioxide
Lead oxide sulfate
(Pb2O(SO4))
Silicic acid, lead salt
Lead-dinitrate
Cadmium-fluoride
Cadmium
1,3,5-
tris(oxiranylmethyl)-1,3,5-
triazine-2,4,6(
Lead Oxide
Trilead bis(carbonate)
dihydroxide
Lead(II,IV)-oxide
Cadmium-sulphide
Cadmium-oxide
Diboron-trioxide
1,2-bis(2-
methoxyethoxy)ethane
formamide
2,2'-dichloro-4,4'-
methylenedianiline
phenolphthalein
Lead-diazide
1,2-
Benzenedicarboxylic
acid, bis(2-
methoxyethyl
Pentazinc-chromate-
octahydroxide
Trilead-diarsenate

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[19006 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

ATP Crimp Dies
for the Tape Crimp
Module and ATP-101
& 301 Press

[192880057](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19006-0003](#)