

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0194290045](#)
Status: **Active**
Overview: [MX150L Industrial Sealed Connector System](#)
Description: MX150L 8 Circuit Panel Mount Plug for 14-22 AWG Wire, Through Hole Flange Assembly, with Gasket, Black

Documents:

3D Model	Packaging Specification PK-19429-001-001 (PDF)
Drawing (PDF)	Brochure (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-19417-001-001 (PDF)	

Agency Certification

UL E152602

General

Product Family	Crimp Housings
Series	19429
Application	Power, Wire-to-Wire
Comments	For Outside or Inside Panel Mount Application. IP67 rated; conforms to UL 1977. NOT suitable for automotive applications with requirements such as USCAR-2, USCAR-25, GMW3191, AK Testing, J2030, Volvo Technology Requirements, and Toyota Connector Spec (
Overview	MX150L Industrial Sealed Connector System
Product Name	MX150L
UPC	822348615131

Physical

Circuits (maximum)	8
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Lock to Mating Part	Yes
Net Weight	15.206/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	5.84mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact 18.0A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-19429-001-001
Product Specification	PS-19417-001-001
Sales Drawing	SD-19429-013



EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Not Relevant

Not Contained

Search Parts in this Series

[19429 Series](#)

Mates With

[19418 MX150L Receptacle Assemblies](#)

Use With

[19417 MX150L Male Crimp Terminals](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19429-0045](#)