

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0347084013](#)


**Status:** **Active**

**Overview:** [Stac64 Single, Multi-Pocket and Hybrid Header System](#)

**Description:** Stac64 4 Bay Right-Angle Headers, 76 Circuits, Bay A 16 Circuit Signal Header, Polarization A; Bay B 20 Circuit Signal Header, Polarization B; Bay C 20 Circuit Signal Header, Polarization C; Bay D 20 Circuit Signal Header, Polarization D, Tray

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-31300-892-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



*Series image - Reference only*

**General**

Product Family	PCB Headers
Series	<a href="#">34708</a>
Application	Automotive, Power, Wire-to-Board
Comments	Bay A 16 Circuits Stac64 Right Angle Signal Header, Polarization A. Bay B 20 Circuits Stac64 Right Angle Signal Header, Polarization B. Bay C 20 Circuits Stac64 Right Angle Signal Header, Polarization C. Bay D 20 Circuits Stac64 Right Angle Signal, Polarization D
Overview	<a href="#">Stac64 Single, Multi-Pocket and Hybrid Header System</a>
Product Name	Stac64
UPC	884982692183

**Physical**

Breakaway	No
Circuits (Loaded)	76
Circuits (maximum)	76
Color - Resin	Black, Brown, Gray, Green
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	33.343/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.36mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +100°C
Termination Interface: Style	Through Hole

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per - D(2021)4569-DC (8 July 2021)

Boric acid

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[34708](#) Series

**Mates With**

[31408](#) USCAR 2.54mm (.100") Pitch Receptacle, [31372](#) 5.25mm (.206") Pitch Hybrid Receptacle Assembly, [34729](#) 2.54mm (.100") Pitch Stac64 Right Angle Receptacle

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	500V

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	040
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260

**Material Info****Reference - Drawing Numbers**

Packaging Specification	PK-31300-892-001
Sales Drawing	SD-34708-400-001

This document was generated on 10/06/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34708-4013](#)