

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0444281204](#)  
**Status:** **Active**  
**Overview:** Micro-Fit Connector System  
**Description:** Micro-Fit BMI Header, Surface Mount Compatible, Dual Row, Right-Angle, without Snap-in Plastic Peg PCB Lock, 12 Circuits, Tin (Sn) Plating

**Documents:**

<a href="#">3D Model</a>	<a href="#">Test Summary 444280001-TS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Symbol Footprint Data SYM-44428-12046-001 (PDF)</a>
<a href="#">Product Specification PS-44300-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-44428-001-001 (PDF)</a>	

**Agency Certification**


CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">44428</a>
Application	Board-to-Board, Power, Wire-to-Board
Comments	High Temperature Square Pin Solder Type Polarized to Mating Part
Overview	<a href="#">Micro-Fit Connector System</a>
Product Name	Micro-Fit BMI
UPC	800756097633

**Physical**

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.738/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	3.50mm
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	3.00mm
Plating min - Mating	5.080µm
Plating min - Termination	5.080µm
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contained Per -  
D(2021)4569-DC (8  
July 2021)  
Benzo(ghi)perylene  
Octanoic acid,  
2,2,3,3,4,4,5,5,6,6,7,7,8,8,8-  
pen  
Dodecamethylcyclhexasiloxane  
Decamethylcyclpentasiloxane  
Octamethylcycltetrasiloxane  
Disodium 3,3'-[[1,1'-  
Biphenyl]-4,4'-  
Diylbis(Azo)  
1,2-  
Benzenedicarboxylic  
acid, bis(3-  
methylbutyl)  
1,2-diethoxyethane  
Dibutyltin-dichloride  
C.I. Direct Black 38  
Ammonium-  
pentadecafluorooctanoate  
Phenol, 2-(2H-  
benzotriazol-2-yl)-4,6-  
bis(1,1-dim  
2-ethylhexyl 10-  
ethyl-4,4-dioctyl-7-  
oxo-8-oxa-3,  
Dibutylbis(pentane-2,4-  
dionato-O,O')tin  
2-(2H-Benzotriazol-2-  
yl)-4,6-  
ditertpentylphenol  
2-(2H-Benzotriazol-2-  
yl)-4-(tert-butyl)-6-  
(sec-b  
1,2-  
Benzenedicarboxylic

**China RoHS**

Surface Mount Compatible (SMC) Yes  
Temperature Range - Operating -40° to +105°C  
Termination Interface: Style Through Hole

#### Electrical

Current - Maximum per Contact 8.5A  
Voltage - Maximum 600V

#### Solder Process Data

Duration at Max. Process Temperature (seconds) 005  
Lead-free Process Capability WAVE  
Max. Cycles at Max. Process Temperature 001  
Process Temperature max. C 260

#### Material Info

#### Reference - Drawing Numbers

Packaging Specification PK-44428-001-001  
Product Specification PS-44300-001-001  
Sales Drawing SD-44428-001-001  
Symbol/Footprint Data SYM-44428-1204\_6-001  
Test Summary 444280001-TS-000

acid, dihexyl ester, bra  
diisohexyl phthalate  
1,2-  
Benzenedicarboxylic  
acid, dipentyl ester, br  
Zirconia  
Aluminosilicate  
Refractory Ceramic  
Fibr  
Nonadecafluorodecanoic  
acid (PFDA) and its  
sodiu  
Tris(4-nonylphenyl,  
branched and linear)  
phosphi  
Perfluorobutane  
sulfonic acid (PFBS)  
and its sal  
Fluoranthene  
Pyrene  
Dodecachloropentacyclo[12.2.1.16,9.02,13.05,10]o  
Dioctyltin dilaurate,  
stannane, dioctyl-,  
bis(co  
Perfluorononan-1-  
oic acid  
(2,2,3,3,4,4,5,5,6,6,7  
Perfluorohexane-1-  
sulphonic acid and its  
salts  
Dipentyl phthalate  
Cobalt-dichloride  
Alkanes, C10-13,  
chloro  
Bis(tributyltin) oxide  
Lead chromate  
Lead chromate  
molybdate sulfate red  
Tris(2-chloroethyl)  
phosphate  
bis(2-methoxyethyl)  
ether  
1,2-Dimethoxyethane  
1,2-bis(2-  
methoxyethoxy)ethane  
Decabromodiphenylether  
Diboron-trioxide  
Cadmium-oxide  
Lead(II,IV)-oxide  
Lead  
Cadmium  
Lead-dinitrate  
Lead-titanium-trioxide  
Pentalead-tetraoxide-  
sulphate  
Tetralead-trioxide-  
sulphate  
Dioxobis(stearato)trilead  
Lead titanium  
zirconium oxide  
Cyanamide, lead(2+)  
salt (1:1)  
Sulfurous Acid, Lead  
Salt, Dibasic

Silicic acid (H<sub>2</sub>Si<sub>2</sub>O<sub>5</sub>),  
barium salt (1:1),  
lead-  
[Phthalato(2-)]dioxotrilead  
4-aminoazobenzene  
N,N-  
Dimethylformamide  
Phenanthrene  
Imidazolidine-2-thione

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[44428](#) Series

**Mates With**

[44133](#) Micro-Fit BMI Panel Mount  
Receptacle Housing, [44764](#) Micro-Fit BMI  
Receptacle Header, [44769](#) Micro-Fit BMI  
Receptacle Header

This document was generated on 08/31/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[44428-1204](#)