

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0622030575](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Impact Backplane Press-In Tool

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)


**General**

Product Family	Application Tooling
Series	<a href="#">207123</a>
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	887191 189642
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**  
Application Tooling Documents

ATS-622030575, TM-622018799



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[207123](#) Series

**Use With**

[76845](#) Impact 100 Ohm Vertical Orthogonal Backplane Signal Module Assembly, 4-Pair by 8 Column

**Application Tooling** | **FAQ**

**Description**

**Product #**

Impact 100 Ohm [1713481828](#)

4 Pair Vertical Orthogonal Header, Dual Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, 0.254µm Gold

Impact 100 Ohm [768451805](#)

4 Pair Vertical Orthogonal Header, Unguided, Open Endwall, 8 Columns, 96 Circuits, Pin Length 5.50mm, Plated Through Hole

Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 768451807

4 Pair Vertical  
Orthogonal Header,  
Unguided, Open  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 100 Ohm 768451824

4 Pair Vertical  
Orthogonal Header,  
Unguided, Dual  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 768451825

4 Pair Vertical  
Orthogonal Header,  
Unguided, Dual  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 768451827

4 Pair Vertical  
Orthogonal Header,  
Unguided, Dual  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 768451828

4 Pair Vertical  
Orthogonal Header,  
Unguided, Dual  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

Impact 100 Ohm 768453805

4 Pair Vertical  
Orthogonal Header,  
Left Guide, Open  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 768453807

4 Pair Vertical  
Orthogonal Header,

Left Guided, Open  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 100 Ohm 768453808

4 Pair Vertical  
Orthogonal Header,  
Left Guided, Open  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 100 Ohm 768455807

4 Pair Vertical  
Orthogonal Header,  
Right Guided, Open  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 100 Ohm 768457804

4 Pair Vertical  
Orthogonal Header,  
Left Guide, Right  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 768457805

4 Pair Vertical  
Orthogonal Header,  
Left Guide, Right  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free

Impact 100 Ohm 768457807

4 Pair Vertical  
Orthogonal Header,  
Left Guided, Right  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free

Impact 100 Ohm 768457808

4 Pair Vertical  
Orthogonal Header,  
Left Guide, Right  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole

Dimension 0.39mm,  
Lead-Free  
Impact 100 Ohm 768459804  
4 Pair Vertical  
Orthogonal Header,  
Right Guide, Left  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.46mm,  
Lead-Free  
Impact 100 Ohm 768459807  
4 Pair Vertical  
Orthogonal Header,  
Right Guided, Left  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 4.90mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead Free  
Impact 100 Ohm 768459808  
4 Pair Vertical  
Orthogonal Header,  
Right Guide, Left  
Endwall, 8 Columns,  
96 Circuits, Pin  
Length 5.50mm,  
Plated Through Hole  
Dimension 0.39mm,  
Lead-Free

This document was generated on 02/27/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62203-0575](#)