

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638114200](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** PremiumGrade Hand Crimp Tool for 2.54mm MX64 Terminals, 18-22 AWG

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207129</a>
Comments	Prototype and field repair. Type: 4A
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	N/A
Tool Type	Hand Crimp Tool
UPC	756054736920
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Physical**

Net Weight 428.885/g

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents  
ATS-6381142HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Not Relevant

Not Relevant

Not Contained

**Search Parts in this Series**

[207129 Series](#)

**Use With**

Loose Piece Terminals

**Application Tooling** | [FAQ](#)

**Description** | **Product #**

2.54mm Pitch MX64 Terminal, Gold [334670003](#)

(Au) Plating, 22 AWG, Right Reel Payoff, Also used with MX123 Female Receptacle Housing

2.54mm Pitch MX64 Terminal, Gold [334670004](#)

(Au) Plating, 22 AWG, Left Reel Payoff, Also used with MX123 Female Receptacle Housing

2.54mm Pitch MX64 Terminal, Gold [334670005](#)

(Au) Plating, 18-20

AWG, Right Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334670006  
Terminal, Gold  
(Au) Plating, 18-20  
AWG, Left Reel  
Payoff, Also used  
with MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680001  
Terminal, Tin (Sn)  
Plating, 22 AWG,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680002  
Terminal, Tin (Sn)  
Plating, 22 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680003  
Terminal, Tin (Sn)  
Plating, 18-20 AWG,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 334680004  
Terminal, Tin (Sn)  
Plating, 18-20 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347361001  
Terminal, Silver  
Plating, 22 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347361002  
Terminal, Silver  
Plating, 18-20 AWG,  
Left Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347362001  
Terminal, Silver  
Plating, 22 AWG,  
Right Reel Payoff,  
Also used with  
MX123 Female  
Receptacle Housing  
2.54mm Pitch MX64 347362002  
Terminal, Silver  
Plating, 18-20 AWG,  
Right Reel Payoff,  
Also used with

This document was generated on 10/07/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63811-4200](#)