

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638250600](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for HNF Female Terminals


Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207129
Comments	Die sets are not sold separately; the complete hand tool needs to be ordered to obtain the die set.. Type: 4C
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	PremiumGrade
Tool Type	Hand Crimp Tool
UPC	884982757066
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers
Application Tooling Documents [ATS-6382506HM-001](#)



EU ELV
Not Relevant

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	

Not Contained Per -
ED/61/2018 (27 June 2018)

Halogen-Free Status
Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[207129](#) Series

Use With
[94518](#) HNF Female Terminals for Double Standard Thick Wall Insulation Metric Wires

Application Tooling Description	FAQ Product #
High Normal Force Tabs, Tin Plated Brass, AWG 14-18	945180201

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63825-0600](#)