


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0503728100**  
**Status:** **Active**  
**Overview:** Micro-Latch Wire-to-Board Connector System  
**Description:** 2.00mm Pitch, Micro-Latch Female Crimp Terminal, Tin (Sn) Plating, 22-26 AWG, Bag

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-51160-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification PS-51160-006-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-52968-006-001 (PDF)</a>
<a href="#">Product Specification 510650000-PS-000 (PDF)</a>	<a href="#">Product Specification PS-52968-007-001 (PDF)</a>
<a href="#">Product Specification 510651000-PS-000 (PDF)</a>	<a href="#">Product Specification PS-53717-002-001 (PDF)</a>
<a href="#">Product Specification PS-51089-001-001 (PDF)</a>	<a href="#">Product Specification PS-54111-002-001 (PDF)</a>
<a href="#">Product Specification PS-51089-005-001 (PDF)</a>	<a href="#">Product Specification PS-55533-004-001 (PDF)</a>
<a href="#">Product Specification PS-51090-004-001 (PDF)</a>	<a href="#">Application Specification 510900001-000 (PDF)</a>
<a href="#">Product Specification PS-51090-005-001 (PDF)</a>	<a href="#">Packaging Specification SPK-50372-001-001 (PDF)</a>
<a href="#">Product Specification PS-51090-009-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-51090-016-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-51090-017-001 (PDF)</a>	



Series image - Reference only

**General**

Product Family	Crimp Terminals
Series	50372
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	<u>Micro-Latch Wire-to-Board Connector System</u>
Packaging Alternative	<u>503728000 (Reel)</u>
Product Name	Mi II, Micro-Latch
UPC	800753352704

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	26.800/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40mm max.
Wire Size AWG	22, 24, 26
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	2.5A
Voltage - Maximum	125V

**Material Info**

**Reference - Drawing Numbers**

Application Specification	510900001-000
Crimp Specification	CS-50372-001-001
Packaging Specification	SPK-50372-001-001
Product Specification	510650000-PS-000, 510651000-PS-000, PS-51089-001-001, PS-51089-005-001, PS-51090-004-001, PS-51090-005-001, PS-51090-009-001, PS-51090-016-001, PS-51090-017-001, PS-51160-001-001,

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

50372 Series

**Use With**

51065 Micro-Latch Receptacle Housing<br>51089 , 51090 Mi II Receptacle Housings

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for 11030043

Micro-Fit Terminals

PremiumGrade Hand638235100

Crimp Tool for Micro-

Latch, DuraClik, and

Servo Motor Encoder

Female Terminals,

22-26 AWG

**Japan**

**Description**

**Product #**

Sales Drawing

PS-51160-006-001, PS-52968-006-001,  
PS-52968-007-001, PS-53717-002-001,  
PS-54111-002-001, PS-55533-004-001  
503720000-SD-000

Extraction Tool 573216000

This document was generated on 12/22/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[50372-8100](#)