

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0622018659](#)
Status: **Active**
Overview:
Description: Daughter Card Module Installation Press-In Tool for 5-Pair by 16-Column Assemblies

General

Product Family	Application Tooling
Series	207123
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	applicationtooling@molex.com
Overview	application_tooling
Product Name	PremiumGrade
Tool Type	Press-Fit Insertion Tool
UPC	883906116170
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents [ATS-622018659, TM-622018799](#)

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

China RoHS

Search Parts in this Series

[207123](#) Series

Use With

Impact Daughtercard Signal Module Assembly [76060](#) , [76780](#)

Application Tooling | FAQ

Description	Product #
Impact 85 Ohm Plus 5 Pair Right-Angle Daughtercard, Unguided, 16 Columns, 240 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1704801026
Impact 85 Ohm Plus 5 Pair Right-Angle Daughtercard, Left Guided, 16 Columns, 240 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1704803026
Impact 85 Ohm Plus 5 Pair Right-Angle Daughtercard, Right Guided, 16 Columns, 240 Circuits, Plated Through Hole Dimension 0.39mm, Lead Free	1704805026
Impact 100 Ohm 5 Pair Right-Angle Daughtercard Receptacle, Unguided, 16	760601016

Columns, 240
Circuits, Plated
Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 760601026
5 Pair Right-Angle
Daughtercard
Receptacle,
Unguided, 16
Columns, 240
Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 760603016
5 Pair Right-Angle
Daughtercard
Receptacle, Left
Guided, 16 Columns,
240 Circuits, Plated
Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 760603026
5 Pair Right-Angle
Daughtercard
Receptacle, Left
Guided, 16 Columns,
240 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 760603126
5 Pair Right-Angle
Daughtercard
Receptacle, Left
Guided, 16 Columns,
240 Circuits, Plated
Through Hole
Dimension 0.39mm,
Polarizing Key
Position A, Lead-
Free
Impact 100 Ohm 760605016
5 Pair Right-Angle
Daughtercard
Receptacle, Right
Guided, 16 Columns,
240 Circuits, Plated
Through Hole
Dimension 0.46mm,
Lead-Free
Impact 100 Ohm 760605026
5 Pair Right-Angle
Daughtercard
Receptacle, Right
Guided, 16 Columns,
240 Circuits, Plated
Through Hole
Dimension 0.39mm,
Lead-Free
Impact 100 Ohm 760605166
5 Pair Right-Angle
Daughtercard

Receptacle, Right
Guided, 16 Columns,
240 Circuits, Plated
Through Hole
Dimension 0.39mm,
Polarizing Key
Position A, Lead-
Free, with ESD Clip

This document was generated on 02/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62201-8659](#)