

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0622030580](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Impact Backplane Press-In Tool

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207123</a>
Comments	See Tooling Specification (PDF) Above
Function	Insertion
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	Impact
Tool Type	Press-Fit Insertion Tool
UPC	887191189659
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents [ATS-622030580](#)

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

**China RoHS**

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207123](#) Series

**Use With**

[76985](#) Impact 100 Ohm Vertical Orthogonal Backplane Signal Module Assembly, 5-Pair by 10 Column Assemblies)

**Application Tooling**

**Description**

**FAQ**

**Product #**

Impact 100 Ohm [769851105](#)

5 Pair Vertical Orthogonal Header Unguided, Open Endwall, 10 Columns, 150 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.46mm, Lead-Free

Impact 100 Ohm [769851108](#)

5 Pair Vertical Orthogonal Header Unguided, Open Endwall, 10 Columns, 150 Circuits, Pin Length 5.50mm, Plated Through Hole Dimension 0.39mm, Lead-Free

Impact 100 Ohm [769851125](#)

5 Pair Vertical Orthogonal Header Unguided, Dual Endwall, 10 Columns, 150 Circuits, Pin Length

5.50mm, Plated  
Through Hole  
Dimension 0.46mm,  
Lead-Free  
Impact 100 Ohm 769851128  
5 Pair Vertical  
Orthogonal Header  
Unguided, Dual  
Endwall, 10  
Columns, 150  
Circuits, Pin Length  
5.50mm, Plated  
Through Hole  
Dimension 0.39mm,  
Lead-Free  
Impact 100 Ohm 769857104  
5 Pair Vertical  
Orthogonal Header  
Left Guide, Right  
Endwall, 10  
Columns, 150  
Circuits, Pin Length  
4.90mm, Plated  
Through Hole  
Dimension 0.46mm,  
Lead-Free  
Impact 100 Ohm 769857105  
5 Pair Vertical  
Orthogonal Header  
Left Guide, Right  
Endwall, 10  
Columns, 150  
Circuits, Pin Length  
5.50mm, Plated  
Through Hole  
Dimension 0.46mm,  
Lead-Free  
Impact 100 Ohm 769857107  
5 Pair Vertical  
Orthogonal Header  
Left Guide, Right  
Endwall, 10  
Columns, 150  
Circuits, Pin Length  
4.90mm, Plated  
Through Hole  
Dimension 0.39mm,  
Lead-Free  
Impact 100 Ohm 769857108  
5 Pair Vertical  
Orthogonal Header  
Left Guide, Right  
Endwall, 10  
Columns, 150  
Circuits, Pin Length  
5.50mm, Plated  
Through Hole  
Dimension 0.39mm,  
Lead-Free

This document was generated on 02/27/2021

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[62203-0580](#)