

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638815600](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: [Mini-Mac Applicator](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Application Tooling
Series	207127
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	applicationtooling@molex.com
Overview	Application Tooling
Product Name	Mini-Mac
Tool Type	Applicator
UPC	822348765614
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info

Reference - Drawing Numbers

Application Tooling Documents

638815600-001, TM-638800000-001, TM-638800000SP-001, TM-640160065-001, TM-640160065CN-001, TM-640160065DE-001, TM-640160065FR-001, TM-640160065IT-001, TM-640160065JP-001, TM-640160065KR-001, TM-640160065MY-001, TM-640160065PL-001, TM-640160065RU-001, TM-640160065SK-001, TM-640160065SP-001, TM-640160065TH-001, TM-640160065TW-001, TM-640160065VN-001

Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

China RoHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[207127 Series](#)

Use With

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

Application Tooling

FAQ

Description

Product #

Open Barrel Star Ring , Tin-Plated Brass, for 14-18 AWG Wire Range, Stud Size 6 (M3.5)	190840004
Open Barrel Star Ring , Tin-Plated Brass, for 14-18 AWG Wire Range, Stud Size 8 (M4)	190840005
Open Barrel Star Ring , Tin-Plated Brass, for 14-18 AWG Wire Range, Stud Size 10 (M5)	190840006
Open Barrel Star Ring , Tin-Plated Steel, for 14-18 AWG Wire Range, Stud Size 6 (M3.5)	190840007
Open Barrel Star Ring , Tin-Plated Steel, for 14-18 AWG Wire Range, Stud Size 8 (M4)	190840008

Open Barrel Star 190840009
Ring , Tin-Plated
Steel, for 14-18 AWG
Wire Range, Stud
Size 10 (M5)
Open Barrel Ring , 190850004
Tin-Plated Brass, for
14-18 AWG Wire,
Stud Size 6 (M3.5)
Open Barrel Ring , 190850005
Tin-Plated Brass, for
14-18 AWG Wire,
Stud Size 8 (M4)
Open Barrel Ring , 190850006
Tin-Plated Brass, for
14-18 AWG Wire,
Stud Size 10 (M5)
Open Barrel Ring , 190850007
Tin-Plated Steel, for
14-18 AWG Wire,
Stud Size 6 (M3.5)
Open Barrel Ring , 190850008
Tin-Plated Steel, for
14-18 AWG Wire,
Stud Size 8 (M4)
Open Barrel Ring , 190850009
Tin-Plated Steel, for
14-18 AWG Wire,
Stud Size 10 (M5)

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63881-5600](#)