

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0639036900**  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** FineAdjust Applicator for Mini-Fit TPA2 Crimp Terminals, 0.50mm<sup>2</sup>, 0.75mm<sup>2</sup> and 18-20 AWG wires

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Application Tooling
Series	<a href="#">207127</a>
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	<a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>
Overview	<a href="#">Application Tooling</a>
Product Name	FineAdjust, Mini-Fit TPA2
Tool Type	Applicator
UPC	889056421232
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents

ATS-639036900-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638004900-001, TM-638004900CN-001, TM-638004900DE-001, TM-638004900FR-001, TM-638004900IT-001, TM-638004900JP-001, TM-638004900KR-001, TM-638004900MY-001, TM-638004900PL-001, TM-638004900RU-001, TM-638004900SK-001, TM-638004900SP-001, TM-638004900TH-001, TM-638004900TW-001, TM-638004900VN-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[207127](#) Series

**Use With**

Molex TM-3000: [638017200](#) , [638017300](#) , Molex TM-4000: [638017600](#) , Molex TM-2000: [638008300](#) , [638008400](#) , and Most Industry Standard Presses or Wire Process Machines

**Application Tooling**

**Description**

**FAQ**

**Product #**

Mini-Fit TPA2/ Sigma Female Crimp Terminal, Phosphor Bronze, Pre-Plated Tin (Sn), 18-20 AWG, 1.42-2.10mm Insulation Diameter, Reel	<a href="#">1727183111</a>
Mini-Fit TPA2/ Sigma Female Crimp Terminal, Brass, Pre-Plated Tin (Sn), 18-20 AWG, 1.42-2.10mm	<a href="#">1727183121</a>

Insulation Diameter,  
Reel  
Mini-Fit TPA2/ 1727653121  
Sigma Male Crimp  
Terminal, Brass,  
Pre-Plated Tin  
(Sn), 18-20 AWG,  
1.42-2.10mm  
Insulation Diameter,  
Reel  
Mini-Fit TPA2/ 2029883141  
Sigma Female Crimp  
Terminal, Copper  
Alloy, Post-Plated  
Gold (Au), 18-20  
AWG, 1.42-2.10mm  
Insulation Diameter,  
Reel  
Mini-Fit TPA2/ 2029883241  
Sigma Female Crimp  
Terminal, Copper  
Alloy, Post-Plated  
Tin (Sn), 18-20AWG,  
1.42-2.10mm  
Insulation Diameter,  
Reel  
Mini-Fit TPA2/ 2030703141  
Sigma Male Crimp  
Terminal, Copper  
Alloy, Post-Plated  
Gold (Au), 18-20  
AWG, 1.42-2.10mm  
Insulation Diameter,  
Reel  
Mini-Fit TPA2/ 2030703241  
Sigma Male Crimp  
Terminal, Copper  
Alloy, Post-Plated  
Tin (Sn), 18-20  
AWG, 1.42-2.10mm  
Insulation Diameter,  
Reel

This document was generated on 10/07/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63903-6900](#)