

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0755455100](#)
Status: **Active**
Overview: [EXTreme PowerMass High-Current Connectors](#)
Description: EXTreme PowerMass 7.40mm Pitch, 40A per module, 1 Circuit, Vertical Receptacle, Lead-Free

Documents:

[3D Model](#) [Packaging Specification PK-75541-200-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

Application tooling part link


Application Tooling Part Link 62100-5900

General

Product Family PCB Receptacles
 Series [75545](#)
 Application Board-to-Board, Power
 Comments 40A per contact
 Overview [EXTreme PowerMass High-Current Connectors](#)
 Product Name EXTreme PowerMass
 UPC 800756673387

Physical

Circuits (Loaded) 1
 Circuits (maximum) 1
 Color - Resin Black
 Durability (mating cycles max) 250
 Flammability 94V-0
 Glow-Wire Capable No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part No
 Material - Metal High Performance Alloy (HPA)
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin High Temperature Thermoplastic
 Net Weight 2.465/g
 Number of Rows 2
 Orientation Vertical
 PC Tail Length 4.72mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 3.18mm
 Packaging Type Tray
 Pitch - Mating Interface 3.33mm
 Pitch - Termination Interface 3.33mm
 Polarized to Mating Part No
 Polarized to PCB No
 Stackable No
 Surface Mount Compatible (SMC) Yes
 Temperature Range - Operating -40° to +105°C
 Termination Interface: Style Through Hole - Compliant Pin



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[75545](#) Series

Mates With

[75561](#) EXTreme PowerMass PCB Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Vertical Receptacle [621005900](#)
 Power Terminal
 Removal Tool

Electrical

Current - Maximum per Contact	40.0A
Grounding to PCB	No
Voltage - Maximum	600V

Material Info**Reference - Drawing Numbers**

Packaging Specification	PK-75541-200-001
Sales Drawing	SD-75545-101-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75545-5100](#)