

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0764605016](#)
Status: **Active**
Overview: [Impact Backplane Connector and Cable Assembly System](#)
Description: [Impact 100 Ohm 2 Pair Right-Angle Daughtercard Receptacle, Right Guided, 16 Columns, 96 Circuits, Plated Through Hole Dimension 0.46mm, Lead-Free](#)

Documents:

3D Model	Packaging Specification PK-70873-592-001 (PDF)
Drawing (PDF)	Test Summary TS-76460-0001-001 (PDF)
3D Model (PDF)	Symbol Footprint Data SYM-76460-5016-001 (PDF)
Product Specification PS-76060-999-001 (PDF)	Symbol Footprint Data SYM-76460-5016REV-A1-001 (PDF)
Application Specification AS-76060-990-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-76060-9999-001 (PDF)	

Agency Certification


UL E29179

General

Product Family	Backplane Connectors
Series	76460
Application	Conventional, Coplanar, Daughtercard
Application Tooling Documents	TM-622018799-001
Component Type	PCB Receptacle
Overview	Impact Backplane Connector and Cable Assembly System
Product Name	Impact
UPC	884982772090

Physical

Circuits (Loaded)	96
Circuits (maximum)	96
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	9.745/g
Number of Columns	16
Number of Pairs	2
Number of Rows	6
Orientation	Right Angle
PC Tail Length	1.20mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	Yes
Stackable	No



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76460 Series](#)

Mates With

[76455](#) Impact 100 Ohm Vertical Backplane Header, [76450](#) Impact 100 Ohm Right Angle Male Header

Temperature Range - Operating -55° to +85°C
Termination Interface: Style Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact 0.75A
Data Rate 25.0 Gbps
Impedance 100Ω
Shield Type N/A
Shielded No
Voltage - Maximum 30V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-76060-990-001, AS-76060-9999-001
Electrical Model Document EE-76460-001-050G-001, EE-76460-001-25G-001
Packaging Specification PK-70873-592-001
Product Specification PS-76060-999-001
S-Parameter Model SP-76460-001-025-001, SP-76460-001-050-001
Sales Drawing SD-76460-004-001
Symbol/Footprint Data SYM-76460-5016-001, SYM-76460-5016_REV-A1-001
Test Summary TS-76460-0001-001

This document was generated on 10/04/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76460-5016](#)