

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0764953807](#)
Status: **Active**
Overview: Impact Backplane Connector and Cable Assembly System
Description: Impact 85 Ohm Plus 4 Pair RAM Signal Module, Left Guided, 8 Columns, 96 Circuits, Pin Length 4.90mm, Plated Through Hole Dimension 0.39mm, Lead Free

Documents:

| | |
|--|--|
| Drawing (PDF) | Packaging Specification PK-70873-041-001 (PDF) |
| Product Specification PS-170540-999-001 (PDF) | Symbol Footprint Data SYM-76495-3807-001 (PDF) |
| Application Specification AS-76060-990-001 (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification


UL E29179

General

| | |
|-------------------------------|--|
| Product Family | Backplane Connectors |
| Series | 76495 |
| Application | Coplanar |
| Application Tooling Documents | TM-622018799-001 |
| Component Type | Right Angle Male |
| Electrical Model | Yes |
| Overview | Impact Backplane Connector and Cable Assembly System |
| Product Name | Impact |
| UPC | 887191541204 |

Physical

| | |
|--------------------------------|--------------------------------|
| Circuits (Loaded) | 96 |
| Circuits (maximum) | 96 |
| Color - Resin | Gray |
| Durability (mating cycles max) | 200 |
| First Mate / Last Break | No |
| Flammability | 94V-0 |
| Guide to Mating Part | Yes |
| Keying to Mating Part | None |
| Material - Metal | High Performance Alloy (HPA) |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Tin |
| Material - Resin | High Temperature Thermoplastic |
| Net Weight | 17.359/g |
| Number of Columns | 8 |
| Number of Pairs | 4 |
| Number of Rows | 12 |
| Orientation | Right Angle |
| PC Tail Length | 1.20mm |
| PCB Locator | No |
| PCB Retention | None |
| PCB Thickness - Recommended | 1.00mm |
| Packaging Type | Tray |
| Pitch - Mating Interface | 1.35mm, 1.90mm |
| Pitch - Termination Interface | 1.35mm, 1.90mm |
| Plating min - Mating | 0.762µm |
| Polarized to PCB | No |
| Stackable | No |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -55° to +85°C |
| Termination Interface: Style | Through Hole - Compliant Pin |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76495 Series](#)

Mates With

[170340](#) Impact 85 Ohm Plus 4 Pair, Right Angle Daughtercard

Electrical

| | |
|-------------------------------|-----------------|
| Current - Maximum per Contact | 0.75A |
| Data Rate | 25.0 Gbps |
| Impedance | 85Ω |
| Shield Type | N/A |
| Shielded | No |
| Voltage - Maximum | 30V AC (RMS)/DC |

Solder Process Data

| | |
|------------------------------|-----|
| Lead-free Process Capability | N/A |
|------------------------------|-----|

Material Info**Reference - Drawing Numbers**

| | |
|---------------------------|--------------------|
| Application Specification | AS-76060-990-001 |
| Electrical Model Document | EE-76495-0002-001 |
| Packaging Specification | PK-70873-041-001 |
| Product Specification | PS-170540-999-001 |
| S-Parameter Model | SP-76495-0002-001 |
| Sales Drawing | SD-76495-002-001 |
| Symbol/Footprint Data | SYM-76495-3807-001 |

This document was generated on 10/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[76495-3807](#)