

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0873811037](#)  
**Status:** **Active**  
**Overview:** [Milli-Grid Connector System](#)  
**Description:** 2.00mm Pitch Milli-Grid Receptacle, Surface Mount, Top Entry, 0.051µm Gold (Au) Plating, without Locating Peg, 10 Circuits, Lead-Free

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 873810001-PK-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-87368-0001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Brochure (PDF)</a>
<a href="#">Product Specification PS-87380-002-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 503940001-AS-000 (PDF)</a>	

**Agency Certification**

CSA	LR19980
UL	E29179

**General**


Product Family	PCB Receptacles
Series	<a href="#">87381</a>
Application	Board-to-Board, Signal
Comments	Without Pegs
Overview	<a href="#">Milli-Grid Connector System</a>
Product Name	Milli-Grid
UPC	884982768048

**Physical**

Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	25
Flammability	94V-0
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.248/g
Number of Rows	2
Orientation	Vertical
PCB Locator	Yes
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.051µm
Plating min - Termination	1.905µm
Polarized to PCB	Yes
Stackable	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	1.9A
Voltage - Maximum	125V



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[87381](#) Series

**Mates With**

[87758](#) Vertical, Through Hole, Stackable PCB Header, [87759](#) Vertical, Surface Mount, Stackable PCB Header, [87760](#) Right Angle, Through Hole, Stackable PCB Header, [87831](#) Vertical, Through Hole PCB Header, [87832](#) Vertical, Surface Mount PCB

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	014
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	265

**Material Info****Reference - Drawing Numbers**

Application Specification	503940001-AS-000
Packaging Specification	873810001-PK-000, PK-87368-0001-001
Product Specification	PS-87380-002-001
Sales Drawing	SD-87381-XXXX-001

This document was generated on 07/30/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87381-1037](#)