


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877159208](#)
Status: **Active**
Overview: PCIe PCI-X Connectors
Description: 1.00mm Pitch, PCI Express Connector, 98 Circuits, Nylon 4/6 Glass-filled, Black Housing, Phosphor Bronze, 0.38µm Gold Solder-tail, Lead-Free

Documents:

3D Model	Packaging Specification PK-87715-207 (PDF)
3D Model (PDF)	Test Summary TS-87715-207-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-87715-200-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Edge Card Connectors
Series	87715
Comments	PCI 8 lanes
Component Type	Edgecard to PCB
Data Rate	8.0 Gbps
Edge Card Thickness	1.57mm
Electrical Model	Yes
High Power Bay (30.0A or more)	No
Orientation	Vertical
Overview	PCIe PCI-X Connectors
Product Name	PCI Express
Standard Based	PCIe
UPC	822348660490

Physical

(p)ower-(s)ignal Configuration	98s - 0p
Circuit Size Range	65-200 Circuits
Circuits (Loaded)	98
Circuits (maximum)	98
Durability (mating cycles max)	50
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Keying to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	5.003/g
PC Tail Length	2.30mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Plating min - Mating	0.381µm
Polarized to Mating Part	Yes
Temperature Range - Operating	-55° to +85°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	1.1A
-------------------------------	------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87715 Series](#)

Mates With

PCI Express Card

Voltage - Maximum 50V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability WAVE
Process Temperature max. C 245

Material Info

Reference - Drawing Numbers

Electrical Model Document EE-87715-002, EE-87715-011, EE-87715-012,
EE-87715-013, EE-87715-014
Packaging Specification PK-87715-207
Product Specification PS-87715-200-001
S-Parameter Model SP-87715-002, SP-87715-011, SP-87715-012,
SP-87715-013, SP-87715-014
Sales Drawing SD-87715-207-001
Signal Integrity Report SI-87715-002
Test Summary TS-87715-207-001

This document was generated on 08/07/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87715-9208](#)