

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877620029](#)
Status: **Active**
Overview: [Milli-Grid Connector System](#)
Description: Milli-Grid Header, Dual Row Dual Body, Surface Mount, Vertical, 10 Circuits, 3.05µm Tin (Sn) Overall Plating, 19.00mm Stacking Height, without Cap, Tube Packaging, Lead-Free

Documents:

Drawing (PDF)	Packaging Specification PK-89990-476-001 (PDF)
Product Specification PS-87761-100-001 (PDF)	Packaging Specification PK-89990-484-001 (PDF)
Application Specification 503940001-AS-000 (PDF)	Packaging Specification PK-89990-485-001 (PDF)
Packaging Specification PK-151033-0001-001 (PDF)	Packaging Specification PK-89990-487-001 (PDF)
Packaging Specification PK-87858-300-000 (PDF)	Test Summary 877610000-TS-000 (PDF)
Packaging Specification PK-89990-475-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification


UL E29179

General

Product Family PCB Headers
 Series [87762](#)
 Application Board-to-Board, Signal
 Overview [Milli-Grid Connector System](#)
 Product Name Dual Body, Milli-Grid
 UPC 822350115889

Physical

Breakaway Yes
 Circuits (Loaded) 10
 Circuits (maximum) 10
 Color - Resin Black
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Capable No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part None
 Mated Height 4.50mm
 Material - Metal Copper Alloy
 Material - Plating Mating Gold
 Material - Plating Termination Tin
 Material - Resin Nylon
 Net Weight 0.245/g
 Number of Rows 2
 Orientation Vertical
 PCB Locator Yes
 PCB Retention None
 Packaging Type Tube
 Pitch - Mating Interface 2.00mm
 Pitch - Termination Interface 2.00mm
 Plating min - Mating 3.048µm
 Plating min - Termination 1.270µm
 Polarized to Mating Part No
 Polarized to PCB No
 Shrouded No
 Stackable No
 Temperature Range - Operating -55° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2021)4569-DC (8
 July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[87762](#) Series

Mates With

[79107](#) Board-to-Board Top Entry Through Hole Receptacle, [79108](#) Board-to-Board FFC/FPC Top Entry Through Hole Receptacle, [79109](#) Board-to-Board Top/Bottom Entry SMT Receptacle, [87381](#) Board-to-Board Top Entry SMT Receptacle

Termination Interface: Style Surface Mount

Electrical

Current - Maximum per Contact 2.0A
Voltage - Maximum 125V

Solder Process Data

Duration at Max. Process Temperature (seconds) 010
Lead-free Process Capability REFLOW
Max. Cycles at Max. Process Temperature 003
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Application Specification 503940001-AS-000
Packaging Specification PK-151033-0001-001, PK-87858-300-000,
PK-89990-475-001, PK-89990-476-001,
PK-89990-484-001, PK-89990-485-001,
PK-89990-487-001
Product Specification PS-87761-100-001
Sales Drawing SD-87762-135-001
Test Summary 877610000-TS-000

This document was generated on 09/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[87762-0029](#)