

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1062840050](#)  
**Status:** **Active**  
**Overview:** [Optical Connectivity Solutions](#)  
**Description:** CXP Optical Cable Assembly (iPass+ ), MTP-to-MTP, Multimode, 50/125µm, Round Cable Assembly, Straight Boot, Standard Bandwidth, OFNP, Cable Diameter 5.40mm, Cable Length 50.00m

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Fiber Optic Assemblies
Series	<a href="#">106284</a>
Boot Type	Straight
Connector to Connector	MTP-to-MTP
Mode	Multimode
Overview	<a href="#">Optical Connectivity Solutions</a>
Product Name	CXP, iPass+, MTP
UPC	883906550196


**Physical**

Cable Length	50.0m
Cable Size	5.40mm
Fiber (Core/Cladding)	50/125µm
Net Weight	1732.320/g
Single Ended	No
Wire/Cable Type	Fiber Optic, Round

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-106284-0001-001
---------------	--------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per - D(2020)4578-DC (25 June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Relevant

Not Contained

**Search Parts in this Series**

[106284 Series](#)

**Mates With**

CXP Optical Transceivers

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106284-0050](#)