

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1068150069](#)
Status: **Active**
Overview: Polymicro Capillary Tubing
Description: Polymicro 1/32" OD Flexible Fused Silica Capillary Tubing, Inner Diameter 300µm, Outer Diameter 794µm, TSP300794

Documents:

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)


General

| | |
|--------------------------------|--|
| Product Family | Capillary Tubing |
| Series | 106815 |
| Application | Industrial, Medical, Research, Scientific, and other |
| Application Notes and Articles | www.molex.com/polymicro/literature.html |
| Capillary Configurator | www.molex.com/polymicro/capillaryconfigurator.html |
| Capillary Series | 1/32" OD |
| Catalog | www.molex.com/polymicro/catalog.html |
| Overview | Polymicro Capillary Tubing |
| Polymicro | Yes |
| Product Name | 1/32" OD |
| Type | Capillary Tubing |
| UPC | 887191311753 |

Physical

| | |
|--------------------------------|---|
| Coating Thickness per Side | 24µm nominal |
| Cutting Style | Laser Cut, Precision Cleave, Saw Cut, Standard Cleave |
| Internal Diameter | 300µm |
| Internal Diameter Tolerance | ± 6µm |
| Material - Coating | Standard Polyimide |
| Material - Tubing | Synthetic Fused Silica |
| Net Weight | 0.890/g |
| Outer Diameter | 794µm |
| Outer Diameter Tolerance | ± 12µm |
| Packaging Type | Spool |
| Proof Tested @ Minimum 100kpsi | 100% for Strength |
| Temperature Range - Operating | -65° to +350°C |
| Tubing Length | 5.0m minimum |

Material Info



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[106815 Series](#)

Use With

www.molex.com/polymicro/capillarytubingaccessories

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106815-0069](#)