



POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH
3	1300630042	C03006A48M020	32	2M +89-0MM (6'7"+3.50-0)
4	1300630150	C04006A48M020	32	2M +89-0MM (6'7"+3.50-0)

FACE VIEW-MALE INSERT





SPECS:  
 OVERMOLD: GRAY PVC W/BLACK STRIP  
 INSERT: BLACK PVC  
 COUPLING NUT: ANODIZED ALUMINUM  
 CABLE: #10AWG GRAY PVC  
 DUAL RATED UL TC/OPEN WIRING & ST00W  
 ELECTRICAL: 600V AC/DC

UPDATED PROFILE EC NO: IPG2014-1160 DRWG:GGUSTAFSON 2013/12/23 CHKD:VOU 2014/01/15 APPR:WOODMAN 2014/05/12	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± .005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.13</td> <td>± .010</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.25</td> <td>± .020</td> </tr> </tbody> </table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± 0.13	± .010	1 PLACE	± 0.25	± .020	DIMENSION STYLE IN/MM DRAWN BY DATE B.RUPERT 01/12/2010 CHECKED BY DATE B.WOODMAN 01/12/2010 APPROVED BY DATE JFMURPHY 2010/01/15	SCALE NTS DESIGN UNITS INCH THIRD ANGLE PROJECTION	TITLE QUICK CHANGE MALE STRAIGHT 3 & 4 POLE PORTABLES MOLEX INCORPORATED DOCUMENT NO. SD-130063-042 SHEET NO. 1 OF 1
		mm	INCH																	
4 PLACES	± ---	± ---																		
3 PLACES	± ---	± .005																		
2 PLACES	± 0.13	± .010																		
1 PLACE	± 0.25	± .020																		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	MATERIAL NO. SEE CHART	SIZE THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																		

POLES	MATERIAL NO.	ENG. NO.	AMPS	LENGTH
3	1300630042	C03006A48M020	32	2M +89-0MM (6'7"+3.50-0)
4	1300630150	C04006A48M020	32	2M +89-0MM (6'7"+3.50-0)

FACE VIEW-MALE INSERT



SPECS:  
 OVERMOLD: GRAY PVC W/BLACK STRIP  
 INSERT: BLACK PVC  
 COUPLING NUT: ANODIZED ALUMINUM  
 CABLE: #10AWG GRAY PVC  
 DUAL RATED UL TC/OPEN WIRING & ST00W  
 ELECTRICAL: 600V AC/DC

UPDATED PROFILE EC NO: IPG2014-1160 DRWG:GGUSTAFSON 2013/12/23 CHKD:VOU 2014/01/15 APPR:WOODMAN 2014/05/12	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± .005</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.13</td> <td>± .010</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.25</td> <td>± .020</td> </tr> </tbody> </table> ANGULAR ±1/2°		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± .005	2 PLACES	± 0.13	± .010	1 PLACE	± 0.25	± .020	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION
			mm	INCH																	
	4 PLACES		± ---	± ---																	
	3 PLACES		± ---	± .005																	
2 PLACES	± 0.13	± .010																			
1 PLACE	± 0.25	± .020																			
	IN/MM	NTS	INCH																		
	DRAWN BY DATE	TITLE																			
	CHECKED BY DATE	QUICK CHANGE MALE STRAIGHT 3 & 4 POLE PORTABLES																			
	APPROVED BY DATE	MOLEX INCORPORATED																			
	MATERIAL NO.	DOCUMENT NO.																			
	SEE CHART	SD-130063-042																			
	SIZE	SHEET NO.																			
	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	1 OF 1																			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300630145](#)