

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1004364011](#)  
**Status:** **Active**  
**Overview:** [Nano-Pitch I/O Interconnect System](#)  
**Description:** Nano-Pitch I/O-to-iPass+ HD Mini SAS Cable Assembly, Straight Plug to Straight Plug, 4x (38 Circuits), 34 AWG, with Latches, 0.30m Length

**Documents:**

<a href="#">3D Model</a>	<a href="#">Drawing (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Cable Assemblies
Series	<a href="#">100436</a>
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Nano-Pitch I/O-to-iPass+ HD
Overview	<a href="#">Nano-Pitch I/O Interconnect System</a>
Product Name	iPass+ HD, Nano-Pitch I/O
UPC	889056479608

**Physical**

Cable Length	0.30m
Circuits (Loaded)	42 (38)
Color - Resin	Black
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Liquid Crystal Polymer, Nylon
Net Weight	33.429/g
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Wire Size AWG	34
Wire/Cable Type	Twinax


**Electrical**

Current - Maximum per Contact	0.5A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-100436-4011-001
---------------	--------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[100436](#) Series

**Mates With**

Nano-Pitch I/O Right Angle Receptacle  
[171982](#) <br> Nano-Pitch I/O Vertical  
Receptacle [171983](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[100436-4011](#)